

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A2	ECR-18-006400	11MAY2018	RG	CW
	A3	ECR-19-003832	18MAR2019	CD	CW
	B	ECR-20-007762	23NOV2020	BS	CW
	C	ECR-24-202635	25APR2024	BS	CW

FOR "T1329034111-000"&"T1329036120-000"  
NEED TO BE COATED INSIDE AND OUTSIDE  
料号 "T1329034111-000"&"T1329036120-000" 需里外喷涂

NOTES:

1. TECHNICAL CHARACTERISTICS:  
BODY MATERIAL: DIE CAST ZINC ALLOY  
SURFACE TREATMENT: SEE TABLE  
DEGREE OF PROTECTION: IP65 (MATED)

注释:

1. 技术参数:  
主体材料: 锌合金  
表面处理: 见表格  
防护等级: IP65(配合)

Technical drawings of the H3A hood assembly showing front, side, and top views with dimensions and labels.

Labels: PG/M THREAD, PG/M 螺纹孔, THREAD DEPTH/ 螺纹深度, (9.5), 5.8, 3.2, 24, 24.5, 36, 11.7, 26.8, 55.8, CE, ETE.

PART NUMBER 料号	PART DESCRIPTION 描述	PG/M THREAD PG/M螺纹孔
T1329033111-000	H3A-MTG-PG11 H3A HOOD, TOP ENTRY PG11, 2 EAR, POWDER COATED, RED RAL2004 H3A上壳, 顶出PG11, 2耳, 红色粉末喷涂 RAL2004	PG11
T1329030111-000	H3A-MTG-PG11 H3A HOOD, TOP ENTRY PG11, 2 EAR, POWDER COATED, GREY H3A上壳, 顶出PG11, 2耳, 灰色粉末喷涂	PG11
T1329030109-000	H3A-MTG-PG9 H3A HOOD, TOP ENTRY PG9, 2 EAR, POWDER COATED, GREY H3A上壳, 顶出PG9, 2耳, 灰色粉末喷涂	PG9
T1329030120-000	H3A-MTG-M20 H3A HOOD, TOP ENTRY M20, 2 EAR, POWDER COATED, GREY H3A上壳, 顶出M20, 2耳, 灰色粉末喷涂	M20X1.5
T1329034111-000	H3A-MTG-PG11 H3A HOOD, TOP ENTRY PG11, 2 EAR, POWDER COATED WITH INSIDE AND OUTSIDE, GREY H3A上壳, 顶出PG11, 2耳, 灰色粉末里外喷涂	PG11
T1329036120-000	H3A-MTG-M20 H3A HOOD, TOP ENTRY M20, 2 EAR, POWDER COATED WITH INSIDE AND OUTSIDE, GREY H3A上壳, 顶出M20, 2耳, 灰色粉末里外喷涂	M20X1.5
T1329035111-100	H3A-MTG-EMC-PG11 H3A EMC HOOD, TOP ENTRY PG11, 2 EAR, Ni PLATED H3A屏蔽上壳, 顶出PG11, 2耳, 镀镍	PG11
T1329035120-100	H3A-MTG-EMC-M20 H3A EMC HOOD, TOP ENTRY M20, 2 EAR, Ni PLATED H3A屏蔽上壳, 顶出M20, 2耳, 镀镍	M20X1.5

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 04MAY2015

DAVID LI

CHK 04MAY2015

CHRIS WANG

APVD 04MAY2015

XU XIANG

PRODUCT SPEC

108-137012

APPLICATION SPEC

114-137012

WEIGHT

-

CUSTOMER DRAWING

NAME  
H3A-MTG/MTG-EMC-PG/M

SIZE CAGE CODE DRAWING NO RESTRICTED TO

A3 - C-T132903X1XXX00

SCALE 1:1 SHEET 1 OF 1 REV C

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-
FINISH	-

MATERIAL

-

-

TE Connectivity

1470-19 (3/13)