

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL RELEASE	15JUN2015	DL	CW
	B	ECR-20-014876	16JUL2021	WQR	CW
	BI	ECR-23-175264	15MAY2023	AC	CW

104
130
27
32
4-Ø4.4
4X M3 THREAD
4X M3 螺纹孔

45.7

4-Ø4.4
108
130
32
35

开孔安装示意图
PANNEL CUT OUT

NOTES:

1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: DIE CAST ALUMINIUM ALLOY
SURFACE TREATMENT: POWDER-COATED, COLOR SEE TABLE
DEGREE OF PROTECTION: IP65 (MATED)

注释:

1. 技术参数:
主体材料: 铝合金
表面处理: 粉末喷涂, 颜色见表格
防护等级: IP65(配合)

SCALE 1:2

139.6
142.2
29.8
(88)

TI430241000-000	H24B-ADM-BO	GRAY	-
TI430241000-100			BODY COATED BOTH INSIDE AND OUTSIDE
TI430241000-200			BODY AND COVER COATED BOTH INSIDE AND OUTSIDE
TI433240000-000		RED	BODY AND COVER COATED, RED
ASSEMBLY PART NUMBER	ASSEMBLY PART DESCRIPTION	COLOR	REMARK

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 15JUN2015

DAVID LI

CHK 15JUN2015

CHRIS WANG

APVD 15JUN2015

XU XIANG

PRODUCT SPEC

108-137013

APPLICATION SPEC

114-137013

WEIGHT

-

NAME
H24B-ADM-BO

TE Connectivity

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-
FINISH	-

MATERIAL

-

-

15JUN2015

15JUN2015

15JUN2015

108-137013

114-137013

-

-

-

-

-

-

-

H24B-ADM-BO

SIZE

A3

CAGE CODE

-

DRAWING NO

C-TI43X24X000X00

RESTRICTED TO

-

Customer Drawing

SCALE

3:4

SHEET

1 OF 1

REV

BI

1470-19 (3/13)