

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20  
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A		INITIAL	22APR2015	DW CW
B		ECR-15-018270	09DEC2015	DW CW
B1		ECR-16-006849	13MAY2016	RL CW
C		ECR-21-122216	03DEC2021	WOR CW

NOTES:  
 1. TECHNICAL CHARACTERISTICS:  
 INSULATION MATERIAL: PC  
 RATED VOLTAGE: 50V  
 RATED CURRENT: SEE TABLE  
 INSULATION RESISTANCE:  $\geq 400M\Omega$   
 RATED IMPULSE VOLTAGE: 0.8KV  
 POLLUTION DEGREE: SEE TABLE  
 FLAMMABILITY: UL94V-0  
 MATING CYCLES: 500 CYCLES  
 OPERATION TEMPERATURE:  $-40\sim+125^{\circ}C$   
 WIRE RANGE: SEE TABLE  
 CONTACT TYPE: CRIMP CONTACT  
 2. CONTACT NEED TO BE ORDERED SEPARATELY.

注释:  
 1. 技术参数:  
 绝缘材料: PC  
 额定电压: 50V  
 额定电流: 见表格  
 绝缘电阻:  $\geq 400M\Omega$   
 额定脉冲电压: 0.8KV  
 污染等级: 见表格  
 阻燃等级: UL94V-0  
 插拔次数: 500次  
 工作温度:  $-40\sim+125^{\circ}C$   
 接线范围: 见表格  
 接线类型: 冷压接  
 2. 端子需要单独订购.

T2111027101-000 & T2111027101-001 SHOWN WITH TUV AND CUL MARK  
 T2111027101-000 & T2111027101-001 带TUV和CUL激光打标

T2111027101-002 SHOWN WITH TUV AND UL MARK  
 T2111027101-002 带TUV和UL激光打标

T2111027101-003 SHOWN WITHOUT LOGO, TUV, UL OR CUL MARK  
 T2111027101-003 不带LOGO, TUV, UL和CUL激光打标

T2111027101-003	HMN-Q-M WITHOUT LOGO HMN-Q 模块公插 不带LOGO	-	-	-	WITHOUT LOGO, TUV, UL OR CUL MARK 不带LOGO, TUV, UL和CUL激光打标
T2111027101-002	HMN-Q3-M HMN-Q3模块公插5A	5A	2	0.08~0.52 mm <sup>2</sup> (28~20 AWG)	WITH LOGO, TUV AND UL MARK 带LOGO, TUV和UL激光打标
T2111027101-001	HMN-Q2-M HMN-Q2模块公插10A	10A	3	0.14~2.5 mm <sup>2</sup> (26~14 AWG)	WITH LOGO, TUV AND CUL MARK 带LOGO, TUV和CUL激光打标
T2111027101-000	HMN-Q1-M HMN-Q1模块公插16A	16A	3	0.14~4 mm <sup>2</sup> (26~12 AWG)	WITH LOGO, TUV AND CUL MARK 带LOGO, TUV和CUL激光打标
PART NUMBER 料号	"X" TYPE "X" 产品型号	"XX" A "XX" 电流	"X" PD "X" 污染等级	WIRE GAUGE 线规	REMARK 备注

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN	David Wang	22APR2015
CHK	Chris Wang	22APR2015
APVD	Xiang Xu	22APR2015
PRODUCT SPEC	108-137067	
APPLICATION SPEC	114-137067	
WEIGHT	-	
CUSTOMER DRAWING	SCALE 1:1	SHEET 1 OF 1

NAME: HMN-Q1/Q2/Q3/Q-M

SIZE: A2 CAGE CODE: 00779 DRAWING NO: T2111027101000 RESTRICTED TO: C

1471-9 (3/13)