

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	14APR2015	DW	CW
	B	ECR-15-018270	09DEC2015	DW	CW
	B1	ECR-16-006849	13MAY2016	RL	CW
	C	ECR-21-111798	28SEP2021	WQR	CW

T2111122201-000 SHOWN,
带 LOGO, 产品型号, 认证标示

T2111122201-001 SHOWN, ALL DIMENSIONS ARE
SAME AS T2111122201-000, EXCEPT WITHOUT LOGO,
TYPE DESCRIPTION, TUV AND CUL MARK
不带 LOGO, 产品型号和认证标示

NOTES:

- TECHNICAL CHARACTERISTICS:
INSULATION MATERIAL: PC
RATED VOLTAGE: 250V
RATED CURRENT: 10A
INSULATION RESISTANCE: $\geq 400M\Omega$
RATED IMPULSE VOLTAGE: 4KV
POLLUTION DEGREE: 3
FLAMMABILITY: UL94V-0
MATING CYCLES: 500 CYCLES
OPERATION TEMPERATURE: $-40\sim+125^{\circ}C$
WIRE RANGE: $0.14\sim 2.5\text{ mm}^2$ (26~14 AWG)
CONTACT TYPE: CRIMP CONTACT
- CONTACT NEED TO BE ORDERED SEPARATELY.
(ORDER No. REFER TO DRAWING: T20200X20XX000)

注释:

- 技术参数:
绝缘材料: PC
额定电压: 250V
额定电流: 10A
绝缘电阻: $\geq 400M\Omega$
额定脉冲电压: 4KV
污染等级: 3
阻燃等级: UL94V-0
插拔次数: 500次
工作温度: $-40\sim+125^{\circ}C$
接线范围: $0.14\sim 2.5\text{ mm}^2$ (26~14 AWG)
接线类型: 冷压接
- 端子需要单独订购.
(订货号参考图面: T20200X20XX000)

T2111122201-001	HMN-012-F WITHOUT LOGO HMN-012模块母插 不带LOGO, 产品型号和认证标示
T2111122201-000	HMN-012-F WITH LOGO HMN-012模块母插
PART NUMBER 料号	PART DESCRIPTION 描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:	TOLERANCES UNLESS OTHERWISE SPECIFIED:
mm	
0 PLC	± 0.1
1 PLC	± 0.15
2 PLC	± 0.2
3 PLC	± 0.25
4 PLC	± 0.3
ANGLES	± 0.5
MATERIAL	FINISH
-	-
-	-

DWN	14APR2015	David Wang
CHK	14APR2015	Chris Wang
APVD	14APR2015	Xiang Xu
PRODUCT SPEC	108-137121	
APPLICATION SPEC	114-137121	
WEIGHT	-	
Customer Drawing		

		TE Connectivity	
		NAME HMN-012-F	
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	©-T2111122201000	-
SCALE		SHEET	REV
1:1		1 OF 1	C

1470-19 (3/13)