

4

3

2

1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION

20

© COPYRIGHT 20 BY -

ALL RIGHTS RESERVED.

REVISIONS

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	22DEC2017	YC	CW

ASSEMBLY STATE OF THE PRODUCT, FOR REFERENCE  
产品装配状态, 供参考

(46)

(18.4)

(Ø13.2)

(15.4)

M3 SCREW, RECOMMENDED  
TIGHTENING TORQUE 0.5 N.m  
M3螺丝, 推荐锁紧力矩0.5 N.m

NOTES:

1. TECHNICAL CHARACTERISTICS:  
INSULATION MATERIAL: PC  
RATED VOLTAGE: 50V  
RATED CURRENT: 10A  
RATED IMPULSE VOLTAGE: 0.8KV  
POLLUTION DEGREE: 3  
FLAMMABILITY: UL94V-0  
WIRE RANGE: 0.14-2.5 mm<sup>2</sup> (26-14 AWG)  
CONTACT TYPE: CRIMP CONTACT

2. CONTACT NEED TO BE ORDERED SEPARATELY.  
(ORDER No. REFER TO DRAWING: T20200X20XX000)

注释:

1. 技术参数:  
绝缘材料: PC  
额定电压: 50V  
额定电流: 10A  
额定脉冲电压: 0.8kV  
污染等级: 3  
阻燃等级: UL94V-0  
接线范围: 0.14-2.5 mm<sup>2</sup> (26-14 AWG)  
接线范围: 冷压接

2. 端子需要单独订购.  
(订货号参考图面: T20200X20XX000)

FOR Ø3-6mm CABLE  
用于直径 Ø3-6mm 电缆线

FOR Ø6-9.5mm CABLE  
用于直径 Ø6-9.5mm 电缆线

SCALE 3:2

T2580012154-701

PIN-Q2-F1

QUINTAX FEMALE CONTACT 1-POS, 10A  
QUINTAX 1-POS 母针, 10A

PART NUMBER  
料号

PART DESCRIPTION  
描述

THIS DRAWING IS A CONTROLLED DOCUMENT.

DWN 22DEC2017

YORK CHEN

CHK 22DEC2017

GINO YAO

APVD 22DEC2017

CHRIS WANG

PRODUCT SPEC

108-137067

APPLICATION SPEC

114-137067

WEIGHT -

CUSTOMER DRAWING

DIMENSIONS:

mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

0 PLC	±-
1 PLC	±-
2 PLC	±-
3 PLC	±-
4 PLC	±-
ANGLES	±-

MATERIAL -

FINISH -

DWN 22DEC2017

YORK CHEN

CHK 22DEC2017

GINO YAO

APVD 22DEC2017

CHRIS WANG

PRODUCT SPEC

108-137067

APPLICATION SPEC

114-137067

WEIGHT -

CUSTOMER DRAWING

NAME  
QUINTAX CONTACT 1-POS, 10A  
PIN-Q2-F1

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	-	©-T2580012154701	-

SCALE	SHEET	OF	REV
2:1	1	1	A

**STE** TE Connectivity

1470-19 (3/13)