


THIS DRAWING IS UNPUBLISHED.	RELEASED FOR PUBLICATION	20
(C) COPYRIGHT 20 BY - ALL RIGHTS RESERVED.		

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	28APR2017	QY	CW



SCALE 1:1

NOTE:
1. TECHNICAL CHARACTERISTICS:
MATERIAL: POLYAMIDE
COLOUR: SEE TABLE
FLAMMABILITY: V0 (UL94)
PROTECTION DEGREE: IP68 (MATED)

注 释:


1. 技术参数:

材 料: 尼龙

颜 色: 见表格

阻燃等级: V0(UL94)

防护等级: IP68(配合)



T3513100001-000	WY-PA6-V0-AD10.0B	PLASTIC FLEXIBLE TUBE AD10.0, BLACK 塑料软管AD10.0(黑色)	6.5X10.0	15	35
T3513130001-000	WY-PA6-V0-AD13.0B	PLASTIC FLEXIBLE TUBE AD13.0, BLACK 塑料软管AD13.0(黑色)	9.5X13.0	20	45
T3513160001-000	WY-PA6-V0-AD15.8B	PLASTIC FLEXIBLE TUBE AD15.8, BLACK 塑料软管AD15.8(黑色)	12.0X15.8	25	55
T3513190001-000	WY-PA6-V0-AD18.5B	PLASTIC FLEXIBLE TUBE AD18.5, BLACK 塑料软管AD18.5(黑色)	14.3X18.5	35	65
T3513210001-000	WY-PA6-V0-AD21.2B	PLASTIC FLEXIBLE TUBE AD21.2, BLACK 塑料软管AD21.2(黑色)	17.0X21.2	40	75
T3513290001-000	WY-PA6-V0-AD28.5B	PLASTIC FLEXIBLE TUBE AD28.5, BLACK 塑料软管AD28.5(黑色)	23.0X28.5	45	100
T3513350001-000	WY-PA6-V0-AD34.5B	PLASTIC FLEXIBLE TUBE AD34.5, BLACK 塑料软管AD34.5(黑色)	29.0X34.5	55	120
T3513430001-000	WY-PA6-V0-AD42.5B	PLASTIC FLEXIBLE TUBE AD42.5, BLACK 塑料软管AD42.5(黑色)	36.0X42.5	65	150
T3513550001-000	WY-PA6-V0-AD54.5B	PLASTIC FLEXIBLE TUBE AD54.5, BLACK 塑料软管AD54.5(黑色)	48.0X54.5	80	190
T3513100101-000	WY-PA6-V0-AD10.0G	PLASTIC FLEXIBLE TUBE AD10.0, GREY 塑料软管AD10.0(灰色)	6.5X10.0	15	35
T3513130101-000	WY-PA6-V0-AD13.0G	PLASTIC FLEXIBLE TUBE AD13.0, GREY 塑料软管AD13.0(灰色)	9.5X13.0	20	45
T3513160101-000	WY-PA6-V0-AD15.8G	PLASTIC FLEXIBLE TUBE AD15.8, GREY 塑料软管AD15.8(灰色)	12.0X15.8	25	55
T3513190101-000	WY-PA6-V0-AD18.5G	PLASTIC FLEXIBLE TUBE AD18.5, GREY 塑料软管AD18.5(灰色)	14.3X18.5	35	65
T3513210101-000	WY-PA6-V0-AD21.2G	PLASTIC FLEXIBLE TUBE AD21.2, GREY 塑料软管AD21.2(灰色)	17.0X21.2	40	75
T3513290101-000	WY-PA6-V0-AD28.5G	PLASTIC FLEXIBLE TUBE AD28.5, GREY 塑料软管AD28.5(灰色)	23.0X28.5	45	100
T3513350101-000	WY-PA6-V0-AD34.5G	PLASTIC FLEXIBLE TUBE AD34.5, GREY 塑料软管AD34.5(灰色)	29.0X34.5	55	120
T3513430101-000	WY-PA6-V0-AD42.5G	PLASTIC FLEXIBLE TUBE AD42.5, GREY 塑料软管AD42.5(灰色)	36.0X42.5	65	150
T3513550101-000	WY-PA6-V0-AD54.5G	PLASTIC FLEXIBLE TUBE AD54.5, GREY 塑料软管AD54.5(灰色)	48.0X54.5	80	190
PART NUMBER 料号	PART DESCRIPTION 描述		∅IDX∅OD 内径(MM)X外径(MM)	STAT.R(MM) 静态弯曲半径(MM)	DYN.R(MM) 动态弯曲半径(MM)

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 28APR2017 QIANG YUAN CHK 28APR2017 GINO YAO APVD 28APR2017 CHRIS WANG		 TE Connectivity	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±. 1 PLC ±. 2 PLC ±. 3 PLC ±. 4 PLC ±. ANGLES ±. FINISH		NAME PLASTIC FLEXIBLE TUBE	
		PRODUCT SPEC - APPLICATION SPEC -		SIZE A2	
MATERIAL - -		WEIGHT -		CAGE CODE 00779	
		CUSTOMER DRAWING		DRAWING NO C-T3513XXXX01000	
				RESTRICTED TO -	
				SCALE 2:1	
				SHEET 1 OF 1	
				REV A	