




THIS DRAWING IS UNPUBLISHED.
RELEASED FOR PUBLICATION
20
ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	INITIAL	29AUG2017	CH	CW
	AI	ECR-24-229772	25DEC2024	BS	RB

- NOTES:
1. TECHNICAL CHARACTERISTICS:
BODY MATERIAL: SPCC
BODY SURFACE: ZINC PLATED
 2. WIRE RANGE: 10-20mm².
 3. MOUNTING RAIL: 35mm STANDARD DIN RAIL.

注释:
1. 技术参数:
主体材料: 冷轧板
主体表面处理: 镀锌

2. 夹线范围: 10-20mm².
3. 适用导轨: 35mm标准DIN导轨.

OBSOLETE

M4 SCREW,
RECOMMENDED TIGHTENING TORQUE 1.2Nm
M4螺丝, 推荐扭力矩为1.2Nm

T3930102001-000	SKTP10-20SC	CABLE SHIELDED CLIP WITH LOCKING PIECE (WIRE RANGE 10-20) 电缆屏蔽夹子, 卡片式(通线10-20)
PART NUMBER 零件料号	PART DESCRIPTION 零件描述	

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN 29AUG2017 CHARLIE.HU	TE Connectivity SKTP10-20SC		
		CHK 29AUG2017 GINO.YAO			
		APVD 29AUG2017 CHRIS.WANG			
		PRODUCT SPEC			
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:	NAME		
	0 PLC	±-	SIZE A3		
	1 PLC	±-			
	2 PLC	±-			
	3 PLC	±-			
	4 PLC	±-			
		ANGLES	CAGE CODE		
		FINISH	DRAWING NO		
MATERIAL			RESTRICTED TO		
			SCALE 3:2		
			SHEET 1 OF 1		
			REV AI		
			CUSTOMER DRAWING		