

P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING	01.04.2020	SI	SI

# TAMPER-PROOF LABELS OVERVIEW



SERIES	PART NO.	DESCRIPTION	MATERIAL	TTDS
MV	A03662-000	MV-254097-10-8A	SV7000, Polyester silver (0,077 mm), Acrylic adhesive with „VOID“ Pattern	TTDS-084

Quantity per roll: 10.000 PCs

Labels across: 3






Winding: outside

length of roll: 42,4 m



All dimensions in mm [inch]

labels are centered on the liner as long as not declared separately

LABEL BUILD DETAILS		TOLERANCES mm [INCH]		THIS DRAWING IS A CONTROLLED DOCUMENT		DWN S. Iser / 01.04.2020 DATE		TE Connectivity			
	SUBSTRATE	LABEL HEIGHT:	±0,3 [0,012]	DIMENSIONS mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED	CHK S. Iser / 01.04.2020 DATE	APVD S. Iser / 01.04.2020 DATE	Name			
	ADHESIVE	LABEL WIDTH:	±0,3 [0,012]			Name					
	LINER	WEB WIDTH:	±0,8 [0,031]			PRODUCT SPEC DATE	Tamper-proof Label Size „254097“				
		VERTICAL REPEAT:	±0,8 [0,031]*			APPLICATION SPEC DATE	WEIGHT	0,025 g	SIZE	A3	
		HORIZONTAL REPEAT:	±0,8 [0,031]*			MATERIAL	FINISH	CAGE CODE	C2290	DRAWING NO	©-TAMPER-PROOF
		PRINT POSITIONING:	±0,8 [0,031]*			SEE TABLE		RESTRICTED TO			
		LEFT MARGIN:	±0,4 [0,016]								
		QUANTITY:	-0% +2%								
		*NON ACCUMULATING									
CUSTOMER DRAWING						SHEET 1 of 1		REV A1			

TAMPER-PROOF SERIES