



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	13MAY2020	GK	DB

### LABEL AND LINER DESIGN



### PRESENTATION



All dimensions in mm [Inch]

**TE PN: D12463-000**

**OUTSIDE WOUND (BACK SLIT CENTRED)**  
**LABEL ACROSS: 1**  
**PER ROLL QTY: 54.86m / 180 feet**

TOLERANCES mm [INCH]	
LABEL HEIGHT:	$\pm 0.3$ [.012]
LABEL WIDTH:	$\pm 0.3$ [.012]
WEB WIDTH:	$\pm 0.8$ [.031]
VERTICAL REPEAT:	$\pm 0.8$ [.031]*
HORIZONTAL REPEAT:	$\pm 0.8$ [.031]*
PRINT POSITIONING:	$\pm 0.8$ [.031]*
LEFT MARGIN:	$\pm 0.4$ [.016]
QUANTITY:	-0 % +2 %
*NON ACCUMULATING	

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ±
	2 PLC ±
	3 PLC ±
	4 PLC ±
	ANGLES ±
MATERIAL SEE TABLE	FINISH GLOSS

MATERIAL	POLYVINYL FLUORIDE (TEDLAR®)		
ADHESIVE TYPE	PERMANENT ACRYLIC		
LINEAR	BROWN KRAFT		
DWN GOPALAKRISHNA HV CHK D.BURGAT APVD D.BURGAT	13MAY2020 13MAY2020 13MAY2020	TE Connectivity	
PRODUCT SPEC TTDS-005 APPLICATION SPEC	NAME TEDLAR® LABEL-WHITE-CONTINUOUS-WITH TRACTOR FEED 12.7mm x 54.8m (0.5inch x 180ft)	RESTRICTED TO	
WEIGHT 95g	SIZE A2	CAGE CODE FB1U7	DRAWING NO C=TTVF050WE-180
CUSTOMER DRAWING	SCALE NTS	SHEET 1 of 1	REV A