



REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A1	NEW DRAWING FORMAT	12MAY2020	GK	DB

LABEL AND LINER DESIGN

PRESENTATION



**OUTSIDE WOUND
LABEL ACROSS: 4
PER ROLL QTY: 10,000**

All dimensions in mm [Inch]

TE PN: 940010-000

MATERIAL	POLYVINYL FLUORIDE (TEDLAR®)
ADHESIVE TYPE	PERMANENT ACRYLIC
LINEAR	BROWN KRAFT

TOLERANCES mm [INCH]
LABEL HEIGHT: ±0.3 [.012]
LABEL WIDTH: ±0.3 [.012]
WEB WIDTH: ±0.8 [.031]
VERTICAL REPEAT: ±0.8 [.031]*
HORIZONTAL REPEAT: ±0.8 [.031]*
PRINT POSITIONING: ±0.8 [.031]*
LEFT MARGIN: ±0.4 [.016]
QUANTITY: -0 % +2 %
*NON ACCUMULATING

THIS DRAWING IS A CONTROLLED DOCUMENT.	
DIMENSIONS: mm [INCHES]	TOLERANCES UNLESS OTHERWISE SPECIFIED:
	0 PLC ±
	1 PLC ± -
	2 PLC ± -
	3 PLC ± -
	4 PLC ± -
ANGLES ± -	
MATERIAL SEE TABLE	FINISH GLOSS

DWN GOPALAKRISHNA HV 12MAY2020	CHK D.BURGAT 12MAY2020	APVD D.BURGAT 12MAY2020	NAME D.BURGAT
PRODUCT SPEC TTDS-005		APPLICATION SPEC	
WEIGHT 0.017g	SIZE A2	CAGE CODE FB1U7	DRAWING NO C=TTVF075025WE10
CUSTOMER DRAWING			RESTRICTED TO -
SCALE NTS		SHEET 1 of 1	REV A1



TEDLAR® LABEL - WHITE - 4 ACCROSS
19.05mm x 6.4mm (0.75inch x 0.2inch)