


P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	NEW DRAWING	29NOV2023	GDK	VN



PRODUCT DIMENSIONS

SIZE	AS SUPPLIED		AS RECOVERED			
	MINIMUM EXPANDED I.D (D)		MAXIMUM RECOVERED I.D (d)		WALL THICKNESS AFTER RECOVERY (NOM) (W)	
	mm.	in.	mm.	in.	mm.	in.
1.2/0.6	1.20	0.047	0.60	0.024	0.40	0.016
1.6/0.8	1.60	0.063	0.80	0.031	0.40	0.016
2.4/1.2	2.40	0.094	1.20	0.047	0.50	0.020
3/1.5	3.20	0.126	1.50	0.059	0.50	0.020
4/2	4.00	0.157	2.00	0.079	0.65	0.026
5/2.5	5.00	0.197	2.40	0.094	0.50	0.020
6.4/3.2	6.40	0.252	3.20	0.126	0.60	0.024
8/4	8.00	0.315	4.00	0.157	0.60	0.024
9.5/4.8	9.50	0.374	4.80	0.189	0.60	0.024
11/5.5	11.00	0.433	5.50	0.217	0.60	0.024
12.7/6.4	12.70	0.500	6.35	0.250	0.60	0.024
15/7.5	15.00	0.591	7.50	0.295	0.80	0.031
16.5/7.3	16.50	0.650	7.30	0.287	0.80	0.031
20/10	20.00	0.787	9.50	0.374	0.80	0.031
25.4/12.7	25.40	1.000	12.70	0.500	0.90	0.035
26/13	26.00	1.024	12.50	0.492	0.90	0.035
32/16	32.00	1.260	14.00	0.551	0.90	0.035
38/19	38.00	1.496	19.05	0.750	1.00	0.039
51/25	51.00	2.008	25.40	1.000	1.10	0.043

PRODUCT INFORMATION:

- NON-FLAME RETARDANT
- MATERIAL: IRRADIATED MODIFIED POLYOLEFIN SLEEVING
STANDARD COLOURS: BLACK
- SHRINK RATIO: 2:1
- LONGITUDINAL CHANGE 0 TO -10%
- TUBING CUT TO SPECIFIC LENGTHS CAN BE SUPPLIED FROM THE PRODUCT SIZES REFERENCED WITHIN THIS DRAWING

STANDARD CUTTING TOLERANCES (mm)	
CUT LENGTH	TOLERANCE
UPTO TO 9.90mm	±1.50mm
10mm TO 24.90mm	±1.50mm
25mm TO 54.90mm	±1.50mm
55mm TO 99.90mm	±3.00mm
100mm TO 149.90mm	±4.00mm
150mm TO 499.90mm	±5.00mm
500mm AND GREATER	±25.40mm

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 0 PLC ±0.1 1 PLC ±0.1 2 PLC ±0.01 3 PLC ±0.001 4 PLC ±0.0001 ANGLES ± FINISH -
MATERIAL SEE NOTE	-

DWN	29NOV2023
GAGANA D K	
CHK	29NOV2023
BASAVARAJA D A	
APVD	29NOV2023
VLADIMIR NEMEC	
PRODUCT SPEC	RW-2201
APPLICATION SPEC	114-120022
WEIGHT	-
CUSTOMER DRAWING	



NAME		TUGA-GP-SLEEVING		
SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO	
A3	-	©-TUGA-GP-SLEEVING	-	
SCALE	SHEET	OF	REV	
NTS	1	1	A	