

TE P/N	TE CD	Nanonics P/N	Part Description
1589064-1	1589064	TCM019PC0DCC10	Threaded coupling, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 10 centimeters.
1589064-2	1589064	TCM019PC0DXC10	Threaded coupling, circular, metal, 19 position, plug, 28 AWG solid, white PTFE wire, 10 centimeters.
1589064-3	1589064	TCM019PC2DC003	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 3 inches.
1589064-4	1589064	TCM019PC2DC006	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 6 inches.
1589064-6	1589064	TCM019PC2DC012	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 12 inches.
1589064-8	1589064	TCM019PC2DC024	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 24 inches.
1589064-9	1589064	TCM019PC2DC036	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 36 inches.
1-1589064-1	1589064	TCM019PC2DC066	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 66 inches.
1-1589064-2	1589064	TCM019PC2DCC30	Threaded coupling, circular, metal, 19 position, plug, 30awg 7 strand, color coded PTFE wire, 30 centimeters.
1-1589064-3	1589064	TCM019PC2DM036	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches.
1-1589064-4	1589064	TCM019PC2DC020	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, color coded PTFE wire, 20 inches.
1-1589064-5	1589064	TCM019PC0DC036	Threaded coupling, circular, metal, 19 position, plug, 28 AWG solid, color coded PTFE wire, 36 inches.
1-1589064-6	1589064	TCM019PC2DM024	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 24 inches.
1-1589064-7	1589064	TCM019PC2DM012	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 12 inches.
1-1589064-8	1589064	TCM019PC3DM036	Threaded coupling, circular, metal, 19 position, plug, 32 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 36 inches.
1-1589064-9	1589064	TCM019PC2DMC10	Threaded coupling, circular, metal, 19 position, plug, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 10 centimeters.
2-1589064-0	1589064	TCM019PC4DXC11	Threaded coupling, circular, metal, 19 position, plug, 34 AWG 7 strand, white PTFE wire, 11 centimeters