



Nanonics Standard Catalog Part Number Cross-Reference

Revision 2

TE P/N	TE CD	Nanonics P/N	Part Description
7-1589671-2	1589736	JSL009PR2DC012N	Jumper, 1 row, LCP, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 12 inches, 1.0 captive jackscrews.
7-1589671-6	1589736	JSL037PR2DX002N	Jumper, 1 row, LCP, 37 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, white PTFE wire, 2 inches, 1.0 captive jackscrews.
9-1589671-8	1589736	JSM009PR2DC002N	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
9-1589671-9	1589736	JSM009PR2DC006N	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
1589672-9	1589736	JSM015PR2DC001N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1.0 inches, 1.0 captive jackscrews.
1-1589672-0	1589736	JSM015PR2DC002N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
1-1589672-1	1589736	JSM015PR2DC003N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 3 inches, 1.0 captive jackscrews.
1-1589672-2	1589736	JSM015PR2DC006N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
2-1589672-6	1589736	JSM025PR2DC006N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
2-1589672-7	1589736	JSM025PR2GX002N	Jumper, 1 row, metal, 25 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 2 inches, 1.0 captive jackscrews.
6-1589672-1	1589736	JSM051PR2GX002N	Jumper, 1 row, metal, 51 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 2 inches, 1.0 captive jackscrews.
4-1589699-9	1589736	JSM015PR2DC004N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 4 inches, 1.0 captive jackscrews.
5-1589699-5	1589736	JSM025PR2DC1.5N	Jumper, 1 row, metal, 25 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1.5 inches, 1.0 captive jackscrews.
5-1589699-6	1589736	JSM051PR2DC1.5N	Jumper, 1 row, metal, 51 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1.5 inches, 1.0 captive jackscrews.
1589736-1	1589736	JSM015PR2DX003N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, white PTFE wire, 3 inches, 1.0 captive jackscrews.
1589736-2	1589736	JSL037PR2DX003N	Jumper, 1 row, LCP, 37 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, white PTFE wire, 3 inches, 1.0 captive jackscrews.
1589736-3	1589736	JSM037PR2DTC03N	Jumper, 1 row, metal, 37 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, white ETFE M22759/33 wire, 3 centimeters, 1.0 captive jackscrews.
1589736-4	1589736	JSL051PR2GX002	Jumper, 1 row, LCP, 51 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 2 inches.
1589736-5	1589736	JSM037PR2DC001Q	Jumper, 1 row, metal, 37 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1.0 inches, 1.2 captive jackscrews.
1589736-6	1589736	JSM051PR2DC001N	Jumper, 1 row, metal, 51 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1 inch, 1.0 captive jackscrews.
1589736-7	1589736	JSM037PR2DC1.5N	Jumper, 1 row, metal, 37 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1.5 inches, 1.0 captive jackscrews.
1589736-8	1589736	JSM009PR2DM009N	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 9 inches, 1.0 captive jackscrews.
1589736-9	1589736	JSM009PR2DCC30Q	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 30 centimeters, 1.2 captive jackscrews.
1-1589736-0	1589736	JSM015PR2GX006N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 6 inches, 1.0 captive jackscrews.
1-1589736-1	1589736	JSM015PR2GX002N	Jumper, 1 row, metal, 15 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, FEP ribbon cable, 2 inches, 1.0 captive jackscrews.
1-1589736-2	1589736	JSM009PR2DCC80Q	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 80 centimeters, 1.2 captive jackscrews.
1-1589736-3	1589736	JSM009PR2DCC12N	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 12 centimeters, 1.0 captive jackscrews.
1-1589736-4	1589736	JSM025PR2DCC10N	Jumper, 1 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 10 centimeters, 1.0 captive jackscrews.
1-1589736-5	1589736	JSM009PR2DC001N	Jumper, 1 row, metal, 9 position, plug to receptacle, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1 inch, 1.0 captive jackscrews.