

8-1589737-0	1589737	JTM051PP2DX010Q	Jumper, 2 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 10 inches, 1.2 captive jackscrews.
8-1589737-1	1589737	JTL015PP2DX003N	Jumper, 2 row, LCP, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 3 inches, 1.0 captive jackscrews.
8-1589737-2	1589737	JTM015PP2DC024N	Jumper, 2 row, metal, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 24 inches, 1.0 captive jackscrews.
8-1589737-3	1589737	JTM037PP2DX006N	Jumper, 2 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 6 inches, 1.0 captive jackscrews.
8-1589737-4	1589737	JTM065PP2DC2.5N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 2.5 inches, 1.0 captive jackscrews.
8-1589737-5	1589737	JTM065PP0DXM1.6N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 28 AWG solid, white PTFE wire, 1.6 meters, 1.0 captive jackscrews.
8-1589737-6	1589737	JTM065PP2DXM1.6N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30 AWG stranded, white PTFE wire, 1.6 meters, 1.0 captive jackscrews.
8-1589737-7	1589737	JTM065PP0DXM16N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 28 AWG solid, white PTFE wire, 16 meters, 1.0 captive jackscrews.
8-1589737-8	1589737	JTM065PP2DXM16N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30 AWG stranded, white PTFE wire, 16 meters, 1.0 captive jackscrews.
8-1589737-9	1589737	JTM065PP2DCM1.3N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1.3 meters, 1.0 captive jackscrews.
9-1589737-0	1589737	JTM065PP2DCC80N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 80 centimeters, 1.0 captive jackscrews.
9-1589737-1	1589737	JTM037PP2DX008N	Jumper, 2 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 8 inches, 1.0 captive jackscrews.
9-1589737-2	1589737	JTL015PP2DC006N	Jumper, 2 row, LCP, 15 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 6 inches, 1.0 captive jackscrews.
9-1589737-3	1589737	JTM065PP2DMC13.5Q	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30 AWG 7 strand, PTFE wire, color coded per MIL-STD-681, system 1 (10 recurring solid colors), 13.5 centimeters, 1.2 captive jackscrews.
9-1589737-4	1589737	JTM025PP2DCC07N	Jumper, 2 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 7 centimeters, 1.0 captive jackscrews.
9-1589737-5	1589737	JTM051PP2DCC50Q	Jumper, 2 row, metal, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 50 centimeters, 1.2 captive jackscrews.
9-1589737-6	1589737	JTM065PP2DMC50N	Jumper, 2 row, metal, 65 position, plug to plug, 1 to 1, 30AWG 7 strand, color coded PTFE wire, MIL-STD-681, 50 centimeters, 1.0 captive jackscrews.
9-1589737-7	1589737	JTL051PP2DCC50	Jumper, 2 row, LCP, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 50 centimeters.
9-1589737-8	1589737	JTL051PP2DCC09N	Jumper, 2 row, LCP, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 9 centimeters, 1.0 captive jackscrews.
9-1589737-9	1589737	JTL037PP2DXC08N	Jumper, 2 row, LCP, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 8 centimeters, 1.0 captive jackscrews.
1925272-1	1589737	JTL037PP2DXC09N	Jumper, 2 row, LCP, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 9 centimeters, 1.0 captive jackscrews.
1925272-2	1589737	JTM009PP2DXC25N	Jumper, 2 row, metal, 9 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 25 centimeters, 1.0 captive jackscrews.
1925272-3	1589737	JTM025PP2DXC25N	Jumper, 2 row, metal, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 25 centimeters, 1.0 captive jackscrews.
1925272-4	1589737	JTM037PP2DXC25N	Jumper, 2 row, metal, 37 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 25 centimeters, 1.0 captive jackscrews.
1925272-5	1589737	JTL051PP2DCM01N	Jumper, 2 row, LCP, 51 position, plug to plug, 1 to 1, 30 AWG 7 strand, color coded PTFE wire, 1 meter, 1.0 captive jackscrews
1925272-6	1589737	JTS025PP2DX002N	Jumper, 2 row, stainless, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 2 inches, 1.0 captive jackscrews.
1925272-7	1589737	JTS025PP2DX003N	Jumper, 2 row, stainless, 25 position, plug to plug, 1 to 1, 30 AWG 7 strand, white PTFE wire, 3 inches, 1.0 captive jackscrews.