

TE P/N	TE CD	Nanonics P/N	Part Description
8-1589672-7	1589798	JTG051PD2GX002Q	Jumper, 2 row, gold, 51 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 2 inches, 1.2 captive jackscrews.
8-1589672-8	1589798	JTG051PD2GX01.5Q	Jumper, 2 row, gold, 51 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 1.5 inches, 1.2 captive jackscrews.
3-1589673-1	1589798	JTM009PD2DX003N	Jumper, 2 row, metal, 9 position, plug to plug, low to hi in row, 30 AWG 7 strand, white PTFE wire, 3 inches, 1.0 captive jackscrews.
3-1589673-2	1589798	JTM009PD2DX006N	Jumper, 2 row, metal, 9 position, plug to plug, low to hi in row, 30 AWG 7 strand, white PTFE wire, 6 inches, 1.0 captive jackscrews.
6-1589673-4	1589798	JTM015PD2GX012N	Jumper, 2 row, metal, 15 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 12 inches, 1.0 captive jackscrews.
8-1589674-8	1589798	JTM037PD2DC002N	Jumper, 2 row, metal, 37 position, plug to plug, low to hi in row, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.
8-1589674-9	1589798	JTM037PD2DC004N	Jumper, 2 row, metal, 37 position, plug to plug, low to hi in row, 30 AWG 7 strand, color coded PTFE wire, 4 inches, 1.0 captive jackscrews.
9-1589674-0	1589798	JTM037PD2GX012N	Jumper, 2 row, metal, 37 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 12 inches, 1.0 captive jackscrews.
9-1589674-1	1589798	JTM037PD2GX024N	Jumper, 2 row, metal, 37 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 24 inches, 1.0 captive jackscrews.
6-1589675-1	1589798	JTM051PD2DT004N	Jumper, 2 row, metal, 51 position, plug to plug, low to hi in row, 30 AWG 7 strand, white ETFE M22759/33 wire, 4 inches, 1.0 captive jackscrews.
6-1589675-2	1589798	JTM051PD2DXC10N	Jumper, 2 row, metal, 51 position, plug to plug, low to hi in row, 30 AWG 7 strand, white PTFE wire, 10 centimeters, 1.0 captive jackscrews.
5-1589699-7	1589798	JTL025PD2DC1.25N	Jumper, 2 row, LCP, 25 position, plug to plug, low to hi in row, 30 AWG 7 strand, color coded PTFE wire, 1.25 inches, 1.0 captive jackscrews.
5-1589699-9	1589798	JTL025PD2DC010N	Jumper, 2 row, LCP, 25 position, plug to plug, low to hi in row, 30 AWG 7 strand, color coded PTFE wire, 10 inches, 1.0 captive jackscrews.
7-1589699-1	1589798	JTM065PD2GX022N	Jumper, 2 row, metal, 65 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 22 inches, 1.0 captive jackscrews.
7-1589699-3	1589798	JTL009PD2GX012N	Jumper, 2 row, LCP, 9 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 12 inches, 1.0 captive jackscrews.
3-1589729-8	1589798	JTL009PD2GX006N	Jumper, 2 row, LCP, 9 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 6 inches, 1.0 captive jackscrews.
3-1589729-9	1589798	JTL009PD2GX018N	Jumper, 2 row, LCP, 9 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 18 inches, 1.0 captive jackscrews.
1589798-1	1589798	JTM015PD2DX006N	Jumper, 2 row, metal, 15 position, plug to plug, hi to low in row, 30 AWG 7 strand, white PTFE wire, 6 inches, 1.0 captive jackscrews.
1589798-2	1589798	JTM015PD2GX006N	Jumper, 2 row, metal, 15 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 6 inches, 1.0 captive jackscrews.
1589798-3	1589798	JTM025PD2GX002N	Jumper, 2 row, metal, 25 position, plug to plug, low to hi in row, 30 AWG 7 strand, FEP ribbon cable, 2 inches, 1.0 captive jackscrews.
1589798-4	1589798	JTM051PD2DC002N	Jumper, 2 row, metal, 51 position, plug to plug, low to hi in row, 30 AWG 7 strand, color coded PTFE wire, 2 inches, 1.0 captive jackscrews.