

General Information

Extended Product Type:	MB10/12.SFL
Product ID:	1SNA111034R0400
EAN:	3472591110340
Catalog Description:	MB10/12.SFL Screw Clamp Terminal Blocks - For 5 x 20 and 5 x 25 fuses - with blown fuse indicator - Grey
Long Description:	- Protect your circuits with 5x20 fuse terminal blocks (fuse not supplied with terminal blocks), - Quickly identify the defective circuit thanks to the blown fuse indicator.

Ordering

Color:	Grey
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85361050

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-A screw clamp
Instructions and Manuals:	1SNC160001C0207-CH-A screw clamp

Dimensions

Product Net Width:	12 mm
Product Net Height:	58 mm
Product Net Depth / Length:	58.5 mm
Product Net Weight:	40 g

Technical

Rated Cross-Section:	10 mm ²
Spacing:	12 mm
Connection Type:	Screw clamp
Function:	Fuse
Number of Levels:	1
Connecting Capacity Main Circuit:	Screw Clamp / Flexible 1x 0.5 ... 10 mm ² Screw Clamp / Rigid 1x 0.5 ... 16 mm ²
Rated Current (I_n):	Main Circuit 10 A
Rated Voltage (U_r):	500 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP10
Insulation Material:	Polyamide

Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Wire Stripping Length:	13.0 mm
Recommended Screw Driver:	6 mm
Tightening Torque:	acc. IEC 60947-1 1.2 N·m Manufacturer 1.4 N·m

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Connecting Capacity Main Circuit UL/CSA:	Screw Clamp / Rigid 1x 18 ... 6 AWG
Connecting Capacity UL/CSA:	Stranded 6 AWG
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

CSA Certificate:	1SND161039A0201
cUL Certificate:	1SND161000A0203
Declaration of Conformity - CE:	1SND225016U1000
EAC Certificate:	1SND161009A1100
Environmental Information:	1SND220021E1002
Instructions and Manuals:	1SNC160001C0207-CH-A screw clamp
RMRS Certificate:	1SND161007A1101
RoHS Information:	1SND230023F0208

Classifications

Object Classification Code:	X
ETIM 4:	EC000899 - Fuse terminal block
ETIM 5:	EC000899 - Fuse terminal block
ETIM 6:	EC000899 - Fuse terminal block

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	126 mm
Package Level 1 Depth / Length:	155 mm

Package Level 1 Height: 64 mm

Package Level 1 Gross Weight: 1 kg

Package Level 1 EAN: 3472591110340

Package Level 2 Units: 250 piece

Package Level 3 Units: 12000 piece

Product Packing Type: Box

