

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ End Sections

General Information

Extended Product Type:	FEMG
Product ID:	1SNA114144R1200
EAN:	3472591141443
Catalog Description:	FEMG End Sections Grey
Long Description:	FEMG - End Sections - Grey - 1.5mm Spacing.

Ordering

Color:	Grey
Minimum Order Quantity:	25 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	2.6 g
----------------------------	-------

Technical

Spacing:	1.5 mm
Function:	End Sections
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	M2.5/6.4G.1 M2.5/6.5.4G.1 M4/6.3G M4/6.5.3G

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Environmental Information:	1SND220090E1000
RoHS Information:	1SND230478F0202

Classifications

Object Classification Code:	X
------------------------------------	---

ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block
ETIM 6:	EC000886 - Endplate and partition plate for terminal block

Container Information

Package Level 1 Units:	25 piece
Package Level 1 Width:	155 mm
Package Level 1 Depth / Length:	200 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.065 kg
Package Level 1 EAN:	3472591141443
Package Level 2 Units:	750 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	500 mm
Package Level 2 Height:	150 mm
Package Level 3 Units:	36000 piece
Product Packing Type:	Bag

