

## General Information

<b>Extended Product Type:</b>	M300/42.EE
<b>Product ID:</b>	1SNA115160R2700
<b>EAN:</b>	3472591151602
<b>Catalog Description:</b>	M300/42.EE Stud Terminal Blocks
<b>Long Description:</b>	M300/42.EE Power Terminal Blocks Feed-through.

## Ordering

<b>Color:</b>	grey
<b>Minimum Order Quantity:</b>	10 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNC160001C0207-CH-D Power terminals
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-D Power terminals

## Dimensions

<b>Product Net Width:</b>	42 mm
<b>Product Net Height:</b>	93 mm
<b>Product Net Depth / Length:</b>	62.5 mm
<b>Product Net Weight:</b>	320 g

## Technical

<b>Rated Cross-Section:</b>	185 mm <sup>2</sup>
<b>Spacing:</b>	42 mm
<b>Connection Type:</b>	Stud
<b>Function:</b>	Feed-through
<b>Number of Levels:</b>	1
<b>Rated Impulse Withstand Voltage (U<sub>imp</sub>):</b>	8 kV
<b>Dielectric Test Voltage:</b>	3500 V
<b>Pollution Degree:</b>	2
<b>Insulation Material:</b>	Polyamide
<b>Mounting on DIN Rail:</b>	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

<b>Tightening Torque:</b>	Cable Lug 15.5 N·m Central Bolt 10 N·m
---------------------------	---

## Technical UL/CSA

<b>Flammability According to UL94:</b>	V2
--	----

## Environmental

<b>Ambient Air Temperature:</b>	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

<b>RoHS Status:</b>	Following EU Directive 2011/65/EU
---------------------	-----------------------------------

## Certificates and Declarations (Document Number)

<b>cUL Certificate:</b>	1SND165000A0203
<b>Declaration of Conformity - CE:</b>	1SND225011U1000
<b>EAC Certificate:</b>	1SND161009A1100
<b>Environmental Information:</b>	1SND220022E1002
<b>Instructions and Manuals:</b>	1SNC160001C0207-CH-D Power terminals
<b>RoHS Information:</b>	1SND230022F0204

## Classifications

<b>Object Classification Code:</b>	X
<b>ETIM 4:</b>	EC000897 - Feed-through terminal block
<b>ETIM 5:</b>	EC000897 - Feed-through terminal block
<b>ETIM 6:</b>	EC000897 - Feed-through terminal block

## Container Information

<b>Package Level 1 Units:</b>	10 piece
<b>Package Level 1 Width:</b>	102 mm
<b>Package Level 1 Depth / Length:</b>	325 mm
<b>Package Level 1 Height:</b>	130 mm
<b>Package Level 1 Gross Weight:</b>	3.2 kg
<b>Package Level 1 EAN:</b>	3472591151602
<b>Package Level 2 Units:</b>	40 piece
<b>Package Level 3 Units:</b>	960 piece
<b>Product Packing Type:</b>	Box

