

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	BJM10
Product ID:	1SNA173613R2300
EAN:	3472591736137
Catalog Description:	BJM 10 4 POLES Jumper Bars
Long Description:	BJM10 - Jumper Bars - 4 poles - - 10mm Spacing.

Ordering

Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNC160001C0207-CH-J Accessories
Instructions and Manuals:	1SNC160001C0207-CH-J Accessories

Dimensions

Product Net Weight:	11 g
----------------------------	------

Technical

Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 57 A
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNC160001C0207-CH-J Accessories
RoHS Information:	1SND230492F0201

Classifications

Object Classification Code:	X
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	10 piece
-------------------------------	----------

Package Level 1 Width:	155 mm
Package Level 1 Depth / Length:	200 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.11 kg
Package Level 1 EAN:	3472591736137
Package Level 2 Units:	700 piece
Package Level 2 Width:	175 mm
Package Level 2 Depth / Length:	227 mm
Package Level 2 Height:	130 mm
Package Level 3 Units:	126000 piece
Product Packing Type:	Bag

