

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ End Sections

General Information

Extended Product Type:	FEDAD10
Product ID:	1SNA399758R2700
EAN:	3472593997581
Catalog Description:	FEDAD10 End Sections Grey
Long Description:	FEDAD10 - End Sections - Grey - 1.5mm Spacing.

Ordering

Color:	Grey
Minimum Order Quantity:	20 piece
Customs Tariff Number:	39269097

Dimensions

Product Net Weight:	3 g
----------------------------	-----

Technical

Spacing:	1.5 mm
Function:	End Sections
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715
Suitable For:	D4/8.SF.I.ADO D4/8.SN.I.ADO

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Certificates and Declarations (Document Number)

Environmental Information:	1SND220090E1000
RoHS Information:	1SND230478F0202

Classifications

Object Classification Code:	X
ETIM 4:	EC000886 - Endplate and partition plate for terminal block
ETIM 5:	EC000886 - Endplate and partition plate for terminal block

ETIM 6:

EC000886 - Endplate and partition plate for terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Gross Weight:	0.06 kg
Package Level 1 EAN:	3472593997581

