

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Protecting Cover Kits

General Information

Extended Product Type:	KCO
Product ID:	1SNK900624R0000
EAN:	3472599006249
Catalog Description:	KCO Protecting Cover Kit - Dark Grey
Long Description:	Mount your protecting cover with the KCO versatile mounting kit (2 end stops, 2 sealing accessories): - Maintain the cover, - Reliably seal the access to the terminal assembly if needed, - Use it as well as an end stop.

Ordering

Color:	Dark Grey
Minimum Order Quantity:	1 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160028D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	10 mm
Product Net Height:	74.4 mm
Product Net Length:	30.2 mm
Product Net Depth / Length:	64.5 mm
Product Net Weight:	47.8 g

Technical

Function:	Protecting Cover Kits
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
Recommended Screw Driver:	4 mm

Suitable For: C6/8.ST4
CO
D35/16.PEN.2L
ZP2.5
ZP2.5-D2
ZP2.5-PE
ZP2.5-S
ZS10
ZS10-PE
ZS10-PE-R1
ZS10-R1
ZS10-S
ZS10-ST
ZS10-ST-1
ZS10-ST-T4
ZS16
ZS16-PE
ZS25
ZS25-PE
ZS35
ZS35-PE
ZS35-PEN
ZS4
ZS4-PE
ZS4-S
ZS4-SF1
ZS4-SF1-R
ZS4-SF1-T
ZS4-SP
ZS4-SP-T2
ZS4-S-R3
ZS4-S-T
ZS

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230507F0202

Classifications

Object Classification Code:	X
E-number:	2925171

Container Information

Package Level 1 Units:	1 piece
Package Level 1 Width:	170 mm
Package Level 1 Depth / Length:	125 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.048 kg
Package Level 1 EAN:	3472599006249
Package Level 2 Units:	100 piece
Package Level 2 Width:	300 mm
Package Level 2 Depth / Length:	400 mm
Package Level 2 Height:	200 mm
Package Level 3 Units:	4800 piece
Product Packing Type:	Bag

