

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	JB12-5
Product ID:	1SNK912305R0000
EAN:	3472599123052
Catalog Description:	JB12-5 Jumper Bar - Orange
Long Description:	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

Ordering

Color:	Orange
Minimum Order Quantity:	20 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160027C0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	12 mm
Product Net Height:	56 mm
Product Net Depth / Length:	31.5 mm
Product Net Weight:	12.9 g

Technical

Spacing:	12 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 76 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	6000 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide

Suitable For: ZK16
ZK16-3P
ZK16-PE
ZK16-PE-3P
ZS25
ZS25-PE

Technical UL/CSA

Maximum Operating Voltage Main Circuit 600 V
UL/CSA:

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230491F0206

Classifications

Object Classification Code: X

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 45 mm

Package Level 1 Depth / Length: 105 mm

Package Level 1 Height: 45 mm

Package Level 1 Gross Weight: 0.279 kg

Package Level 1 EAN: 3472599123052

Package Level 2 Units: 600 piece

Package Level 2 Width: 200 mm

Package Level 2 Depth / Length: 200 mm

Package Level 2 Height: 300 mm

Package Level 3 Units: 9000 piece

Product Packing Type: Box

