

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Jumper Bars

General Information

Extended Product Type:	JB16-5
Product ID:	1SNK916305R0000
EAN:	3472599163058
Catalog Description:	JB16-5 Jumper Bar - Orange
Long Description:	Insulated jumper bar with screw mounting.

Ordering

Color:	Orange
Minimum Order Quantity:	10 piece
Customs Tariff Number:	85369010

Popular Downloads

Data Sheet, Technical Information:	1SNK160032D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	16 mm
Product Net Height:	75.5 mm
Product Net Length:	23.4 mm
Product Net Depth / Length:	23.4 mm
Product Net Weight:	28 g

Technical

Spacing:	16 mm
Function:	Jumper Bars
Rated Current (I_n):	Main Circuit 125 A
Rated Short-time Withstand Current (I_{cw}):	for 1 s 4200 A
Rated Voltage (U_r):	1000 V
Rated Impulse Withstand Voltage (U_{imp}):	8000 V
Dielectric Test Voltage:	2200 V
Pollution Degree:	3
Power Loss:	4 W

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Recommended Screw Driver:	5.5 mm
Suitable For:	M35/16 ZS35 ZS50 ZS50-PE

Technical UL/CSA

Maximum Operating Voltage UL/CSA:	Main Circuit 600 V
Flammability According to UL94:	V0

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

ATEX Certificate:	1SND162004A1708
CB Certificate:	1SND161028A0203
Instructions and Manuals:	1SNK160027C0201
RoHS Information:	1SND230499F0202

Classifications

Object Classification Code:	X
E-nummer:	2925391
ETIM 4:	EC000489 - Cross-connector for terminal block
ETIM 5:	EC000489 - Cross-connector for terminal block
ETIM 6:	EC000489 - Cross-connector for terminal block

Container Information

Package Level 1 Units:	10 piece
Package Level 1 Width:	125 mm
Package Level 1 Depth / Length:	170 mm
Package Level 1 Height:	5 mm
Package Level 1 Gross Weight:	0.28 kg
Package Level 1 EAN:	3472599163058
Package Level 2 Units:	500 piece

Package Level 2 Width: 200 mm

Package Level 2 Depth / Length: 300 mm

Package Level 2 Height: 200 mm

Package Level 3 Units: 24000 piece

Product Packing Type: Bag

