

**EKM-1281-1D1-4x35-2PG-C2**  
**Art.-Nr.: 269328-000 (JOR-96601)**

**Fuse box for lighting application EKM 1281**

- For application inside of lighting poles with min. inner-Ø of 120 mm, with hand holes min. 100 x 300 mm,
- For outdoor application,
- With 1 DIN rail TS 35 (**nonrusting**) for application of modular DIN rail products,
- With 1 fuse holder 16 A / D01-E14 (**fully insulated with nonrusting clips**),
- With adapter piece 6 A
- With 6 A fuse cartridge
- With screw cap
- With terminal block B6665/4 with 4 mantle terminals for up to 2 x 35 mm<sup>2</sup>
- With cable sealing for 1 or 2 underground cables with diameter up to 30 mm
- With 1 compression gland **IP 68 for one luminaire cable, dia. 6-12 mm** and one membrane gland
- With protective cover over mantle terminals providing IP 2X during maintenance (change of fuses),
- Protection class II,
- Degree of protection IP 54 Housing made from impact resistant, flame retardant grey polypropylene
- Cover fixed with screw lock



