

EKM-2020-2D1-E22
Art.-Nr.: 453496-000 (JOR-94248)

Fuse box for lighting application EKM 2020 according to DIN 43628

for installation in lighting columns

- protection class II
 - ingress protection IP 44
 - minimum diameter 84 mm
 - door opening minimum 70 x 240 mm
 - l x w x h: 232 x 69 x 69,5 mm
 - transparent cover with snap lock
 - 2 fuse bases 16 A / D01-E 14
 - 2 screw caps E 14
 - 5 mantle terminals
 - rail connection (brass rails, nickel-plated)
 fully insulated PE- and n- output terminals
 - type of mains: N, L1, L3, L2, PE(N), for all net configurations
 - pre- mounting earthing cable, 10 mm², green / yellow, 400 mm long,
 with captive screw M 8 x 12
 - cable entry: cable clamp for 1 cable to 3 cables 5 x 2,5 – 16 mm²
 - output: 2 cable insertion grommets, 2 x 5 x 2,5 mm²
- Two additional luminaire cables can be routed towards the bottom of the box.

