



EKM-1282-1D1-5S/C-2PG-C2
Art.-Nr.: 766320-000 (JOR-98659)

Fuse box for lighting application EKM 1282

for installation in lighting columns and outdoor application

- protection class II
- ingress protection IP 54
- minimum diameter 120 mm
- door opening minimum 100 x 350 mm
- l x w x h: 338 x 100 x 90 mm
- grey cover with screw
- protection cover
- 5-pin sliding terminal block B 6850 for:
 - 2 cables 5 x 2,5 – 16 mm²
 - 5 sliding terminals
 - rail connection (brass rails, nickel-plated)
 - fully insulated PE- and n- output terminals
- 1 mounting rail TS 35 for application of installation devices
- 1 fuse base 16 A / D01-E 14
- 1 step carrier, complete
- cable entry: cable clamp for 1 cable to 2 cables Ø 22 - 30 mm
- output: 2 compression gland PG 16, cable Ø 9-14 mm

