



COLD SHRINK “ALL-IN-ONE” STRAIGHT JOINTS (CSJA)

FOR POLYMERIC INSULATED CABLES UP TO 42 kV

KEY FEATURES

- Joint body, earthing system and re-jacketing pre-expanded on one holdout system for short and easy installation
- Ergonomically designed spiral holdout for a safe installation with low release forces for the installer
- Single piece joint body with integrated electrical stress control and a Faraday cage
- Silicone rubber joint body with high mechanical expansion capability and a wide application range
- Mechanical connector to IEC 61238-1 is supplied with the kit

TE Connectivity’s (TE) Raychem CSJA “All-In-One” straight joints offer a reliable, fast and easy-to-install jointing system to assure and maintain high network reliability. Our key components are pre-expanded on one holdout system, allowing a very short parking length during cable preparation.

The silicone rubber body provides high dielectric strength, high tear strength, low tension set, and excellent low temperature recovery. Integrated electrical stress control enhanced by factory molded stress cones and a Faraday cage. Void filling stress relief mastics are not necessary.

TE’s Raychem CSJA joints are designed to cover a wide range of applications and to accommodate the variety of cable and conductor types in the networks. The joints accept both mechanical and compression connectors. When shear bolt connectors are used, this is a totally crimpless system.

TE’s Raychem CSJA exceeds CENELEC HD 629.1 requirements which include IEC, BS, VDE and other international specifications.

Customers can count on consistent, high quality products, driven by TE’s proven innovation and backed by our extraordinary customer support.

Cold Shrink "All-In-One" Straight Joint CSJA



PRODUCT SELECTION INFORMATION

Description	Application Range (mm ²)*	Diameter Over Core Insulation	Diameter Over Outer Sheath	Diameter Over Conductor**	Admissible Connector Dimensions*** Max Length	Diameter
CSJA without mechanical connector						
12 kV						
CSJA-12B1/1XU-1XU	95 - 240	18.6 - 28.4	26.0 - 39.0	-	145.0	19.0 - 34.0
CSJA-12B/1XU-1XU	95 - 240	18.6 - 28.4	26.0 - 39.0	-	145.0	19.0 - 34.0
CSJA-12C/1XU-1XU	185 - 300	23.2 - 32.6	30.0 - 44.0	-	145.0	23.0 - 37.0
CSJA-12D/1XU-1XU	240 - 400	25.7 - 33.6	33.0 - 45.0	-	170.0	26.0 - 42.0
CSJA-12E/1XU-1XU	500 - 800	34.4 - 42.2	43.0 - 58.0	-	200.0	34.0 - 50.0
24 kV						
CSJA-24B/1XU-1XU	35 - 185	18.9 - 30.1	26.0 - 41.0	-	145.0	19.0 - 34.0
CSJA-24C/1XU-1XU	95 - 300	23.5 - 34.6	30.0 - 46.0	-	145.0	23.0 - 37.0
CSJA-24D/1XU-1XU	185 - 400	27.4 - 37.8	35.0 - 49.0	-	170.0	26.0 - 42.0
CSJA-24E/1XU-1XU	400 - 630	35.1 - 44.0	43.0 - 57.0	-	200.0	34.0 - 50.0
CSJA-24F/1XU-1XU	800- 1000	43.9 - 53.2	58.5 - 67.0	-	200.0	41.0 - 60.0
36 (42) kV						
CSJA-36D/1XU-1XU	70 - 240	26.2 - 37.6	34.0 - 48.0	-	140.0	26.0 - 38.0
CSJA-36E/1XU-1XU	240 - 630	34.9 - 49.2	42.0 - 61.0	-	200.0	34.0 - 50.0
CSJA-36F/1XU-1XU	500 - 800	42.6 - 53.4	51.0 - 66.0	-	200.0	41.0 - 56.0
CSJA with mechanical connector						
12 kV						
CSJA-12B1/1XU-1XU-M	95 - 240	18.6 - 28.4	26.0 - 39.0	11.0 - 19.2	-	-
CSJA-12B/1XU-1XU-M	95 - 240	18.6 - 28.4	26.0 - 39.0	11.0 - 19.2	-	-
CSJA-12C/1XU-1XU-M	185 - 300	23.2 - 32.6	30.0 - 44.0	15.5 - 23.1	-	-
CSJA-12D/1XU-1XU-M	240 - 400	25.7 - 33.6	33.0 - 45.0	17.8 - 24.6	-	-
CSJA-12E/1XU-1XU-M1	500	33.7 - 36.2	43.0 - 48.0	25.7 - 27.6	-	-
CSJA-12E/1XU-1XU-M2	630	38.0 - 40.0	47.0 - 52.0	29.3 - 32.5	-	-
24 kV						
CSJA-24B/1XU-1XU-M	35 - 150	18.9 - 28.5	26.0 - 39.0	6.8 - 15.0	-	-
CSJA-24C/1XU-1XU-M1	95 - 240	23.5 - 32.6	30.0 - 44.0	11.0 - 19.2	-	-
CSJA-24C/1XU-1XU-M2	120 - 300	24.3 - 34.6	32.0 - 46.0	12.5 - 23.1	-	-
CSJA-24D/1XU-1XU-M	185 - 400	27.4 - 37.8	35.0 - 49.0	15.5 - 24.6	-	-
CSJA-24E/1XU-1XU-M1	500	37.9 - 40.6	46.0 - 52.0	25.7 - 27.6	-	-
CSJA-24E/1XU-1XU-M2	630	41.0 - 44.0	56.0 - 57.0	29.3 - 32.5	-	-
36 (42) kV						
CSJA-36D/1XU-1XU-M	95 - 240	27.8 - 37.6	35.0 - 48.0	11.0 - 19.2	-	-
CSJA-36E/1XU-1XU-M1	240 - 400	34.9 - 42.8	42.0 - 54.0	17.8 - 24.6	-	-
CSJA-36E/1XU-1XU-M2	500	42.6 - 45.6	51.0 - 57.0	25.7 - 27.6	-	-
CSJA-36E/1XU-1XU-M3	630	45.8 - 49.2	56.0 - 61.0	29.3 - 32.5	-	-

* The application range given in the table is based on polymeric insulated cables according to IEC 60502 with stranded circular conductors.

Due to different conductor dimensions and/or cable constructions the minimum and maximum application range may be extendable.

Please contact your local sale representative.

** The diameter over conductor is needed only for kits including TE's BSM connectors. The values given in the selection table refer to aluminum circular conductors and may change for other materials and shapes.

*** 10 mm max. block thickness of connector.

FOR MORE INFORMATION:

TE Technical Support Centers

USA:	+ 1 800 327 6996
Canada:	+ 1 (905) 475-6222
Mexico:	+ 52 (0) 55-1106-0800
Latin/S. America:	+ 54 (0) 11-4733-2200
France:	+ 33 380 583 200
UK:	+ 44 0870 870 7500
Germany:	+ 49 89 6089 903
Spain:	+ 34 916 630 400
Italy:	+ 39 333 250 0915
Benelux:	+ 32 16 508 695
Russia:	+ 7 495-790 790 2-200
China:	+ 86 (0) 400-820-6015

te.com/energy

© 2018 TE Connectivity. All Rights Reserved. EPP-2346-10/18

Raychem, TE Connectivity and the TE connectivity (logo) are trademarks of the TE Connectivity Ltd. family of companies. Other logos, product and Company names mentioned herein may be trademarks of their respective owners. While TE has made every reasonable effort to ensure the accuracy of the information in this brochure, TE does not guarantee that it is error-free, nor does TE make any other representation, warranty or guarantee that the information is accurate, correct, reliable or current. TE reserves the right to make any adjustments to the information contained herein at any time without notice. TE expressly disclaims all implied warranties regarding the information contained herein, including, but not limited to, any implied warranties of merchantability or fitness for a particular purpose. The dimensions in this brochure are for reference purposes only and are subject to change without notice. Specifications are subject to change without notice. Consult TE for the latest dimensions and design specifications.