


COIL: @ +25 °C	
RESISTANCE	700 OHMS ± 10%
NOMINAL VOLTAGE	20.0 VDC
MUST OPERATE	10.6 VDC
MUST RELEASE	1.06 VDC

ENVIRONMENT:

VIBRATION	10	CPS TO	2000	CPS @	20	g's
SHOCK	100	g's	6 ± 1	MS. DURATION		
TEMPERATURE	-65	°C TO	+125	°C		

NOTES: \_\_\_\_\_  
 \_\_\_\_\_  
 \_\_\_\_\_

**CUSTOMER DATA SHEET**



CONTACT RATING: LOW LEVEL TO 2 AMPS  
 @ 28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 4/7/92 CK. 4/7/92 JMB



CUST. C. I. I. STD.  
 CUST. NO. \_\_\_\_\_

TYPE 'HF' RELAY

HF1201C00