


COIL: @ +25° C
 RESISTANCE 27 OHMS ± 10%
 NOMINAL VOLTAGE 5.0 VDC
 MUST OPERATE 2.7 VDC
 MUST RELEASE 0.29 VDC

ENVIRONMENT:
 VIBRATION 10 CPS TO 2000 CPS @ 20 g's
 SHOCK 100 g's 6 ± 1 MS. DURATION
 TEMPERATURE -65 °C TO +125 °C

NOTES: _____

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 5A
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 11/13/96 CK. *W/13/96/RB*

COMMUNICATIONS
INSTRUMENTS, INC.

CUST. C. I. I. STD.
 CUST. NO. _____

TYPE HFWSA RELAY

HFWSA1131L00