


REV. 2 4/6/98

COIL: @ 25°C  
 RESISTANCE 125 OHMS ± 10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 2.8 VDC  
 MUST RELEASE 1.7 VDC MAX, 0.23 VDC MIN.

ENVIRONMENT:  
 VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 4.0 MS MAX.  
RELEASE TIME 7.5 MS MAX.  
CONTACT BOUNCE 1.5 MS MAX.

CUSTOMER DATA SHEET



CONTACT RATING: LOW LEVEL TO 1A  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 5/15/97 *CK JERRY 4/6/98*

**COMMUNICATIONS INSTRUMENTS, INC.**

CUST. QPL  
 CUST. NO. M39016/25-025L

TYPE J1MSD RELAY

**J1MSPD-5XL**