

REV. 1 3/23/99  
DCO 140960


COIL: @ 25°C  
 RESISTANCE 50 OHMS ± 10%  
 NOMINAL VOLTAGE 5.0 VDC  
 MUST OPERATE 2.7 VDC  
 MUST RELEASE 0.22 VDC

ENVIRONMENT:

VIBRATION 10 CPS TO 3000 CPS @ 30 g's  
 SHOCK 75 g's 6 MS. DURATION  
 TEMPERATURE -65 °C TO +125 °C

NOTES: OPERATE TIME 2.0 MS MAX  
RELEASE TIME 1.5 MS MAX  
CONTACT BOUNCE 1.5 MS MAX

CUSTOMER DATA SHEET



TERMINAL VIEW

CONTACT RATING: LOW LEVEL TO 1 AMP  
28 VDC RESISTIVE 100,000 OPERATIONS

DR. R.B. 7/29/97 (CK) JERRY C 3-23-99

**COMMUNICATIONS**  
**INSTRUMENTS, INC.**

CUST. C.I.I. STD.  
 CUST. NO. \_\_\_\_\_

TYPE "MGA" RELAY

**MGAP-5**