


1 PAIR 22 AWG RoHS CABLE



CONSTRUCTION

Single Component

Conductor: 22 AWG 7/30 Tin Plated Copper, 0.030 Inch Diameter

Insulation: 0.010 Inches of XPbT, 0.050 Inch Diameter

Final Assembly

Core: 2 Singles (#1-2) Cabled Together

Binder: Polyester Tape, 25% Overlap

Jacket: 0.034 Inches of Outdoor-Rated XPbT, Color – Black

Diameter: 0.170 Inches Nominal

Print Legend (White Ink): "AWM STYL E 2549 90°C 300V VW-1 MADISON"

CABLE CSA 114/B 90°C 300V ET1 P6HS COMPLIANT™

CABLE CSA II A/B 90 °C 500V F11 R0HS COMPLIANT	
COLOR CODE	
Conductor #	Insulation Color
1	Black
2	White

ELECTRICAL CHARACTERISTICS

Conductor DC Resistance: 0.015 Ohms/ft Nominal @ 20°C


SAFETY CERTIFICATION

UL Recognized: AWM Style 2549 90°C 300 Volts VW-1

CSA Certification: AWM II A/B 90°C 300 Volts FT1

ROHS Compliance: In Accordance to European Directive 2002/95/EC, Issue

13.2.2003



125 Goddard Memorial Drive • Worcester, MA 01603 USA
Tel: (508) 752-2884 Toll-Free: (877) MADISON Fax: (508) 752-4230

Spec Number:	101-3548
--------------	----------

Part Number:	02RGALF007
---------------------	-------------------

Customer:	
-----------	--

Customer #:	
-------------	--

REVISION HISTORY

1	11/04/05	EP	Initial Release	
2	11/07/05	EP	Added P/N	
Prepared By:		E. Piekiniak		Page 1 of 1
Reviewed By:		R. Lemos	B. Morissette	