SAFETY ORGANIZATIONS

THIS FILTER HAS BEEN FORMALLY RECOGNIZED, CERTIFIED DR APPROVED BY THE LISTED AGENCY. THEREFORE, ALL TEST/REQUIREMENTS SPECIFIED IN THE LATEST REVISION OF THE FOLLOWING AGENCY STANDARDS HAVE BEEN MET:

UL RECOGNIZEO: UL 1283 CSA CERTIFIED: CSA 22.2, # 0,0.4,8 VDE APPROVED: EN 133 200

OPERATING SPECIFICATIONS

LINE CURRENT/VOLTAGE: 15 AMP, 120/250 VAC,

10 AMP/40°C, 250 VAC

LINE FREQUENCY: 50-60Hz

MAXIMUM LEAKAGE CURRENT,

EACH LINE TO GROUND:

9.6 μA @ 120V 50Hz 16.6 µA @ 250V 50Hz

OPERATING AMBIENT TEMP. RANGE: -10°C TO +40°C @ RATED CURRENT, In. IN AN AMBIENT, To, HIGHER THAN 40°C, THE MAXIMUM OPERATING

CURRENT, Io, IS AS FOLLOWS: 100 - To $I_0 = I_r$

RELIABILITY SPECIFICATIONS:

STORAGE TEMPERATURE: -40°C TO +85°C HUMIDITY: 21 DAYS @ 40°C 95% RH. CURRENT DVERLOAD TEST: 6 TIMES In FOR 8 SECONDS

CUSTOMER DRAWING CATALOG #15SRBS8-R ECN # LAPPRVO. DATE PJD 07-026555 08NDV07

TEST SPECIFICATIONS:

INDUCTANCE: N/A mH CAPACITANCE: (MEASURED @ IKHz, 0.250VAC MAX., 25°C±1°C)

N/A

LINE TO GROUND: LINE TO LINE: 100pF ± 20% N/A

DISCHARGE RESISTOR: L/G AND L/L I.R.

NO DISCHARGE RESISTOR:

6000M₁ (MIN.) @ 100VDE,


20°C AND 50% RH

RECOMMENDED RECEIVING INSPECTION HIPOT:

LINE TO GROUND: 1500 VAC FOR 1 MINUTE 1450 VDC FOR 1 MINUTE LINE TO LINE:

FILTER APPROVAL:

THE BEST WAY TO SELECT AND QUALIFY A FILTER IS FOR YOUR ENGINEERING TO TEST THE UNIT IN YOUR EQUIPMENT.



50A-50A(MINIMUM) INSERTION LOSS						22	THIRD ANGLE	
FREBLIENCY MHz	1.0	5.0	10	50	100	300	PROJECTION UNLESS OTHERWISE SPECIFIED,	Tyco Electronics CDXCOM PRODUCTS, 620 S. BUTTERFIELD RO. MANGELETM 1L 80060
COMMON dB	/	/	/	3	δ	22	TOLERANCE ID BE ± .025 MATERIAL & FINISH: AS SUPPLIED THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO	POWER LINE FILTER TYCO ELECTRONICS PART NUMBER: 2-6609987-9
DIFF. dB	/	1	/	1	/		TYCO ELECTRONICS COPPORATION AND ITS WORLDYTOS SUBSIDIARIES AND AFFELTAIS. IT MAY NOT BE DISCLOSED TO ANOME OTHER THAN TYCO ELECTRONICS PRESCHEL, WITHOUT VRITTEN AUTHORIZATION PROMITYCO ELECTRONICS CORPORATION. WARDSTREAM, PENNSYLVANIA USA	SCALE: .75: DATE: TOMAROG CATALOG NO. REV DRIG: PUID 15SRBS8-R 1