





4

3

4


2

三 角 法 (THIRD ANGLE PROJECTION)




断面 C-C (SECT.)

断面 D-D (SECT.)



断面 B-B (SECT.)



断面 A-A (SECT.)

注: 1. 通用規格
製品規格 108-5302
取付通用規格 114-5142
取扱説明書 IS-503J

NOTES: 1. APPLICABLE SPEC.
PRODUCT SPEC. 108-5302
APPLICATION SPEC. 114-5142
2. INSTRUCTION SHEET IS-503J

	NYE製: 502H-20-UV (NYE: 502H-20-UV 100%カドニ化処理 (APPLIED LUBRICANT OIL))	錫めっき黄銅 (PRE-TINNED BRASS)	175149-3
175153-2		錫めっき黄銅 (PRE-TINNED BRASS)	175149-2
175153-1		錫めっき黄銅合金 (PRE-TINNED COPPER ALLOY)	175149-1
バッチ端子型番 (L.P. P/N)	仕上 (FINISH)	材料 (MATERIAL)	型番 (P/N)

STE TE Connectivity

C4	REVISED PER ECR-23-176215	M.G.	D.Z.	012-035mm(awg#26-#22)	1.2-2mm	仕様 (NAME) (TAB CONTACT AMP. UNIVERSAL POWER CONN.)	77-コネクタ, アンテナユニバーサルパワーコネクタ
C3	REVISED PER ECR-20-100273	M.G.	D.Z.	材質 (MATERIAL) 参照表	仕様 (SPEC.) 参照表	寸法 (DIM.)	2PLC:±0.20
C2	REV ECR M-006821	OK	TM	DR. 2001.11.19	DESIGNER 2001.11.19	公差 (TOLERANCE)	ANGLE:±3°
C1	REVISED PER ECO-11-005030	RK	HMR	CHK 2001.11.19	APP 2001.11.19	SIZE	B J
LTR	改訂履歴 (REVISION RECORD)	DR.	CHK.	DATE		LOC	C-175149
						REV. (SCALE)	5-1
						REV.	C4
						SHEET	

単位: mm DIMENSIONS IN MM. DO NOT SCALE PRINT

PRINT DATE