

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Component Plugs

General Information

Extended Product Type:	PG5-R2
Product ID:	1SNK900403R0000
EAN:	3472599097353
Catalog Description:	PG5-R2 Component Plug - Dark Grey
Long Description:	- Component holder compatible with 5.2 mm 0.205 in spacing ZS4 feed-through terminal blocks, - Fit components 16 x 16 x 8.5 mm 0.630 x 0.630 x 0.335 in (not supplied with plug) such as resistors, diodes, varistors, - Direct plug-in into the terminal blocks jumper channels, - Maximum dissipated power: 2 W.

Ordering

Color:	Dark Grey
---------------	-----------

Minimum Order Quantity:	20 piece
--------------------------------	----------

Customs Tariff Number:	85369010
-------------------------------	----------

Popular Downloads

Data Sheet, Technical Information:	1SNK160039D0201
---	-----------------

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	10 mm
---------------------------	-------

Product Net Height:	37.9 mm
----------------------------	---------

Product Net Length:	48.9 mm
----------------------------	---------

Product Net Depth / Length:	48.9 mm
------------------------------------	---------

Product Net Weight:	8 g
----------------------------	-----

Technical

Spacing:	9.95 mm
-----------------	---------

Function:	Component Plugs
------------------	-----------------

Rated Voltage (U_r):	250 V
---------------------------------------	-------

Rated Impulse Withstand Voltage (U_{imp}):	4000 V
---	--------

Pollution Degree:	3
--------------------------	---

Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
------------------------------	--

Insulation Material:	Polyamide
-----------------------------	-----------

Suitable For:	ZDP2.5-11
	ZDP2.5-22
	ZK2.5
	ZK2.5-3P
	ZK2.5-4P
	ZK2.5-D2
	ZK2.5-D-CH
	ZP2.5
	ZP2.5-3P
	ZP2.5-4P
	ZP2.5-D2
	ZS4
	ZS4-D2
	ZS4-D-CH
	ZS4-R2
	ZS4-T3
	ZS4-T3-R1

Technical UL/CSA

Flammability According to UL94:	V0
--	----

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C
	Storage -55 ... +110 °C

Resistance to Vibrations acc. to IEC 60068-2-6:	Compliant
--	-----------

RoHS Status:	Following EU Directive 2002/95/EC August 18, 2005 and amendment
---------------------	---

Certificates and Declarations (Document Number)

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

RoHS Information:	1SND230496F0202
--------------------------	-----------------

Classifications

Object Classification Code:	X
E-nummer:	2925159
ETIM 4:	EC002018 - Component plug terminal block
ETIM 5:	EC002018 - Component plug terminal block
ETIM 6:	EC002018 - Component plug terminal block

Container Information

Package Level 1 Units:	20 piece
Package Level 1 Width:	101 mm
Package Level 1 Depth / Length:	120 mm
Package Level 1 Height:	50 mm

Package Level 1 Gross Weight:	0.16 kg
Package Level 1 EAN:	3472599097353
Package Level 2 Units:	160 piece
Package Level 2 Width:	200 mm
Package Level 2 Depth / Length:	300 mm
Package Level 2 Height:	200 mm
Package Level 2 Gross Weight:	1.53 kg
Package Level 3 Units:	15360 piece
Product Packing Type:	Box

