

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Shield Connectors

General Information

Extended Product Type:	SHBP
Product ID:	1SNK900601R0000
EAN:	3472599097377
Catalog Description:	SHBP Shield Connector
Long Description:	- Ensure the continuity of your shield connection, - Various connection solutions available: RILS cable ties, soldering, quick-connect.

Ordering

Minimum Order Quantity:	20 piece
Customs Tariff Number:	74199990

Popular Downloads

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	2.4 mm
Product Net Height:	116 mm
Product Net Length:	11.53 mm
Product Net Depth / Length:	11.5 mm
Product Net Weight:	4.1 g

Technical

Function:	Shield Connectors
Rated Voltage (U_r):	100 V
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Brass
Suitable For:	ZK2.5 ZK2.5-S ZK2.5-SP ZP2.5 ZP2.5-S ZP2.5-SP

Environmental

Ambient Air Temperature:	Operation -55 ... +110 °C Storage -55 ... +110 °C
---------------------------------	--

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230520F0200

Classifications

Object Classification Code: X

ETIM 4: EC002020 - Shield connection clamp

ETIM 5: EC002020 - Shield connection clamp

ETIM 6: EC002020 - Shield connection clamp

Container Information

Package Level 1 Units: 20 piece

Package Level 1 Width: 158 mm

Package Level 1 Depth / Length: 243 mm

Package Level 1 Gross Weight: 0.082 kg

Package Level 1 EAN: 3472599097377

Package Level 2 Units: 500 piece

Package Level 3 Units: 6500 piece

Product Packing Type: Bag

