

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Protecting Covers

General Information

Extended Product Type:	CO
Product ID:	1SNK900604R0000
EAN:	3472599163706
Catalog Description:	CO Protecting Cover - Transparent
Long Description:	- Restrict access to your assembly with the protecting cover CO installed with KCO mounting kit (2 end stops, 2 sealing accessories), - Compatible with SNK feed-through terminal blocks up to 35 mm ² 0 AWG.

Ordering

Color:	Transparent
Minimum Order Quantity:	1 piece
Customs Tariff Number:	39269097

Popular Downloads

Data Sheet, Technical Information:	1SNK160020D0201
Instructions and Manuals:	1SNK160027C0201

Dimensions

Product Net Width:	1000 mm
Product Net Height:	77 mm
Product Net Length:	30.2 mm
Product Net Depth / Length:	30.2 mm
Product Net Weight:	300 g

Technical

Spacing:	1000 mm
Function:	Protecting Covers
Pollution Degree:	3
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	PVC

Suitable For: C6/8.ST4
D35/16.PEN.2L
ZP2.5
ZP2.5-D2
ZP2.5-PE
ZP2.5-S
ZP2.5-SP
ZS10
ZS10-PE
ZS10-PE-R1
ZS10-R1
ZS10-S
ZS10-ST
ZS10-ST-1
ZS10-ST-T4
ZS16
ZS16-PE
ZS25
ZS25-PE
ZS35
ZS35-PE
ZS35-PEN
ZS4
ZS4-PE
ZS4-R1
ZS4-S
ZS4-SF1
ZS4-SF1-R
ZS4-SF1-T
ZS4-SP
ZS4-SP-T2
ZS4-S-

Technical UL/CSA

Flammability According to UL94: V2

Environmental

Ambient Air Temperature: Operation -55 ... +80 °C
Storage -55 ... +80 °C

Resistance to Vibrations acc. to IEC 60068-2-6: Compliant

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230500F0202

Classifications

Object Classification Code: X

E-nummer: 2925163

Container Information

Package Level 1 Units: 1 piece

Package Level 1 Width: 158 mm

Package Level 1 Depth / Length: 243 mm

Package Level 1 Gross Weight: 0.3 kg

Package Level 1 EAN: 3472599163706

Package Level 3 Units: 50 piece

Product Packing Type: Bag

