

SC-JB8-2



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories
→ Short Circuit Bridges

General Information

Extended Product Type:	SC-JB8-2
Product ID:	1SNK900652R0000
EAN:	3472599872967
Catalog Description:	SC-JB8-2 Short circuit bridges - Yellow
Long Description:	- Allow safe short-circuiting of Current Transformers circuits, - Insulated, - Fully operated by screwdriver, - Short circuited fixed position secured thanks to AJS9 tightening, - Adapted hook shape maintains the bridge on the terminal block in the non short-circuited position, - The orange version can be used as fixed jumpers.

Ordering

Color:	Yellow
Minimum Order Quantity:	25 piece
Customs Tariff Number:	85389099

Popular Downloads

Instructions and Manuals:	1SNK160027C0201
----------------------------------	-----------------

Dimensions

Product Net Width:	8 mm
Product Net Height:	24.6 mm
Product Net Depth / Length:	13.9 mm
Product Net Weight:	2 g

Technical

Spacing:	8 mm
Function:	Short Circuit Bridges
Rated Current (I_n):	Main Circuit 5 A
Degree of Protection:	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
Insulation Material:	Polyamide
Mounting on DIN Rail:	G32 (32 x 15 mm Mounting Rail) acc. to IEC 60715 TH35-7.5 (35 x 7.5 mm Mounting Rail) acc. to IEC 60715 TH35-15 (35 x 15 mm Mounting Rail) acc. to IEC 60715 TH15-5.5 (15 x 5.5 mm Mounting Rail) acc. to IEC 60715
Recommended Screw Driver:	3.5 mm

Suitable For: D6/8.ST.RS
ZS10-PE-R1
ZS10-R1
ZS10-ST
ZS10-ST-T4

Technical UL/CSA

Flammability According to UL94: V0

Environmental

Ambient Air Temperature: Operation -55 ... +110 °C
Storage -55 ... +110 °C

RoHS Status: Following EU Directive 2002/95/EC August 18, 2005 and amendment

Certificates and Declarations (Document Number)

Instructions and Manuals: 1SNK160027C0201

RoHS Information: 1SND230528F0200

Classifications

Object Classification Code: X

Container Information

Package Level 1 Units: 25 piece

Package Level 1 Width: 125 mm

Package Level 1 Depth / Length: 170 mm

Package Level 1 Height: 20 mm

Package Level 1 Gross Weight: 0.05 kg

Package Level 1 EAN: 3472599872967

Package Level 2 Units: 500 piece

Package Level 2 Width: 175 mm

Package Level 2 Depth / Length: 227 mm

Package Level 2 Height: 130 mm

Package Level 2 Gross Weight: 1.000 kg

Package Level 3 Units: 24000 piece

Product Packing Type: Bag



