

# SC-JB8-3



TE Connectivity has acquired the DIN Rail Terminal Block product range from ABB

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Short Circuit Bridges

## General Information

<b>Extended Product Type:</b>	SC-JB8-3
<b>Product ID:</b>	1SNK900653R0000
<b>EAN:</b>	3472599872950
<b>Catalog Description:</b>	SC-JB8-3 Short circuit bridges - Yellow
<b>Long Description:</b>	- Allow safe short-circuiting of Current Transformers circuits, - Insulated, - Fully operated by screwdriver, - Short circuited fixed position secured thanks to AJS9 tightening, - Adapted hook shape maintains the bridge on the terminal block in the non short-circuited position, - The orange version can be used as fixed jumpers.

## Ordering

<b>Color:</b>	Yellow
<b>Minimum Order Quantity:</b>	25 piece
<b>Customs Tariff Number:</b>	85389099

## Popular Downloads

<b>Instructions and Manuals:</b>	1SNK160027C0201
----------------------------------	-----------------

## Dimensions

<b>Product Net Width:</b>	8 mm
<b>Product Net Height:</b>	24.6 mm
<b>Product Net Depth / Length:</b>	13.9 mm
<b>Product Net Weight:</b>	3.4 g

## Technical

<b>Spacing:</b>	8 mm
<b>Function:</b>	Short Circuit Bridges
<b>Rated Current (I<sub>n</sub>):</b>	Main Circuit 5 A
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide
<b>Recommended Screw Driver:</b>	3.5 mm
<b>Suitable For:</b>	D6/8.ST.RS ZS10-PE-R1 ZS10-R1 ZS10-ST ZS10-ST-T4

## Technical UL/CSA

**Flammability According to UL94:** V0

## Environmental

**Ambient Air Temperature:** Operation -55 ... +110 °C  
Storage -55 ... +110 °C

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

**Instructions and Manuals:** 1SNK160027C0201

**RoHS Information:** 1SND230528F0200

## Classifications

**Object Classification Code:** X

## Container Information

**Package Level 1 Units:** 25 piece

**Package Level 1 Width:** 125 mm

**Package Level 1 Depth / Length:** 170 mm

**Package Level 1 Height:** 20 mm

**Package Level 1 Gross Weight:** 0.085 kg

**Package Level 1 EAN:** 3472599872950

**Package Level 2 Units:** 500 piece

**Package Level 2 Width:** 175 mm

**Package Level 2 Depth / Length:** 227 mm

**Package Level 2 Height:** 130 mm

**Package Level 2 Gross Weight:** 1.800 kg

**Package Level 3 Units:** 24000 piece

**Product Packing Type:** Bag

