

Products → Low Voltage Products and Systems → Connection Devices → Terminal Blocks Accessories  
→ Jumper Bars

## General Information

<b>Extended Product Type:</b>	JB12-3
<b>Product ID:</b>	1SNK912303R0000
<b>EAN:</b>	3472599123038
<b>Catalog Description:</b>	JB12-3 Jumper Bar - Orange
<b>Long Description:</b>	Facilitate & secure your jumper bar assembly process: - Screwless mounting, - Pre-cut poles for alternated jumpering between terminal blocks, - Insulated, - Positive locking, - Perfectly adapted to low level electrical contact (20mA, 50mV).

## Ordering

<b>Color:</b>	Orange
<b>Minimum Order Quantity:</b>	50 piece
<b>Customs Tariff Number:</b>	85369010

## Popular Downloads

<b>Data Sheet, Technical Information:</b>	1SNK160027C0201
<b>Instructions and Manuals:</b>	1SNK160027C0201

## Dimensions

<b>Product Net Width:</b>	12 mm
<b>Product Net Height:</b>	32 mm
<b>Product Net Depth / Length:</b>	31.5 mm
<b>Product Net Weight:</b>	7.6 g

## Technical

<b>Spacing:</b>	12 mm
<b>Function:</b>	Jumper Bars
<b>Rated Current (<math>I_n</math>):</b>	Main Circuit 76 A
<b>Rated Voltage (<math>U_r</math>):</b>	1000 V
<b>Rated Impulse Withstand Voltage (<math>U_{imp}</math>):</b>	6000 V
<b>Degree of Protection:</b>	acc. to IEC 60529, IEC 60947-1, EN 60529 Main Terminals IP20
<b>Insulation Material:</b>	Polyamide

**Suitable For:** ZK16  
ZK16-3P  
ZK16-PE  
ZK16-PE-3P  
ZS25  
ZS25-PE

## Technical UL/CSA

**Maximum Operating Voltage** Main Circuit 600 V  
**UL/CSA:**

---

**Flammability According to UL94:** V0

## Environmental

**Ambient Air Temperature:** Operation -55 ... +110 °C  
Storage -55 ... +110 °C

---

**RoHS Status:** Following EU Directive 2002/95/EC August 18, 2005 and amendment

## Certificates and Declarations (Document Number)

**Instructions and Manuals:** 1SNK160027C0201

---

**RoHS Information:** 1SND230491F0206

## Classifications

**Object Classification Code:** X

## Container Information

**Package Level 1 Units:** 50 piece

---

**Package Level 1 Width:** 45 mm

---

**Package Level 1 Depth / Length:** 105 mm

---

**Package Level 1 Height:** 45 mm

---

**Package Level 1 Gross Weight:** 0.428 kg

---

**Package Level 1 EAN:** 3472599123038

---

**Package Level 2 Units:** 1500 piece

---

**Package Level 2 Width:** 200 mm

---

**Package Level 2 Depth / Length:** 200 mm

---

**Package Level 2 Height:** 300 mm

---

**Package Level 3 Units:** 96000 piece

---

**Product Packing Type:** Box

