





THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 20
 © COPYRIGHT 20 BY - ALL RIGHTS RESERVED.

REVISIONS
 変更


P	LTR	DESCRIPTION	DATE	DWN	APVD
	D1	REVISED PER ECR-17-017423	29NOV2017	T.S	E.1



22POS(X-KEY)
 : 2-2013325-1
 2-2069573-1
 2-2069574-1



RECOMMEND PC BOARD HOLE PATTERN
 : CONNECTOR MOUNT SIDE
 (NOT ACCUMULATE TOLERANCE)
 PC BOARD THICKNESS : 1.0~1.6±0.1



n	A	B	C	KEY	POS.	COLOR	PART NO
10	35.0	42.3	44.3	X	22	YELLOW	2-2069574-1
						NATURAL	2-2069573-1
						BLACK	2-2013325-1
5	17.5	24.8	26.8	X	12	YELLOW	1-2069574-6
						NATURAL	1-2069573-6
						BLACK	1-2013325-6
3	10.5	17.8	20.2	X	8	YELLOW	1-2069574-4
						BLACK	1-2013325-4

- ①. MATERIAL: HOUSING: 66 NYLON GLASS FILLED (UL94V-0)
 CONTACT: COPPER ALLOY
 RETENTION LEG: PRE-TIN COPPER ALLOY
- ②. FINISH (ALL OVER): NICKEL PLATING 1.27µm MIN
- ③. FINISH (CONTACT AREA): GOLD PLATING 0.38µm MIN AFTER ②
- ④. FINISH (CONTACT TAIL): TIN PLATING 2µm MIN AFTER ②
- 5. THE SHAPE, SIZE AND POSITION OF THE CHARACTER SHOW THE OUTLINE. THEY DON'T SHOW DETAILS.

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: 単位: 耗 mm	TOLERANCES UNLESS OTHERWISE SPECIFIED: 一般公差 ±0.3, ±5°
	0-PLC ±
	1-PLC ±0.5
	2-PLC ±0.13
	3-PLC ±0.013
	4-PLC ±0.0001
	ANGLES ±
MATERIAL 材料	FINISH 仕上
①	② ③ ④

DWN	09MAY2008
M. MAEBASHI	
CHK	09MAY2008
T. KUDO	
APVD	09MAY2008
S. MANABE	
PRODUCT SPEC	108-78336
製品規格	
APPLICATION SPEC	-
取付適用規格	
WEIGHT	-
CUSTOMER DRAWING	

TE TE Connectivity

NAME
名称 DYNAMIC D1900D 3.5mm PITCH
HDR ASSY (V-TYPE)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
A3	00779	C-2013325	-

SCALE 4:1 SHEET 1 OF 2 REV D1

THIS DRAWING IS UNPUBLISHED.

RELEASED FOR PUBLICATION


20

© COPYRIGHT 20 BY -


ALL RIGHTS RESERVED.

REVISIONS





P	LTR	DESCRIPTION	DATE	DWN	APVD
		SEE SHEET 1			



12POS(X-KEY) : 1-2013325-6
 1-2069573-6
 1-2069574-6



8POS(X-KEY) : 1-2013325-4
 1-2069574-4



THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS:
mm

TOLERANCES UNLESS OTHERWISE SPECIFIED:

- 0 PLC ±-
- 1 PLC ±0.5
- 2 PLC ±0.13
- 3 PLC ±0.013
- 4 PLC ±0.0001
- ANGLES ±-
- FINISH -

MATERIAL

DWN 09MAY2008

M. MAEBASHI

CHK 09MAY2008

T. KUDO

APVD 09MAY2008

S. MANABE

PRODUCT SPEC
108-78336

APPLICATION SPEC

WEIGHT

CUSTOMER DRAWING



TE Connectivity

NAME
DYNAMIC D1900D 3.5mmPITCH
HDR ASSY (V-TYPE)

SIZE	CAGE CODE	DRAWING NO	RESTRICTED TO
------	-----------	------------	---------------

A3	00779	C-2013325	-
----	-------	-----------	---

SCALE 4:1	SHEET 2 OF 2	REV D1
-----------	--------------	--------

SEE SHEET 1 OF 2