



REVISIONS				
P	LTR	DESCRIPTION	DATE	APVD
A1		GO TO PRODUCTION	23FEB2023	IQ WJY



PART NUMBER	PART DESCRIPTION	SUB PART NUMBER	POSITION	NAME	MATERIAL	DIM-A	DIM-B	DIM-C	NOTE	NOTE
2377259-6	ELBC-24-SCA-K1-630-E	-	2	-	△2	53	52	29	TYPE SCA E	31.2-38.3 mm
		2377261-6	1	STRESS CONE SIZE E	△1					
2377259-5	ELBC-24-SCA-K1-630-D	-	2	-	△2	46	39	26	TYPE SCA D	27.4-34.6 mm
		2377261-5	1	STRESS CONE SIZE D	△1					
2377259-4	ELBC-24-SCA-K1-630-C	-	2	-	△2	43	40	22	TYPE SCA C	22.8-28.5 mm
		2377261-4	1	STRESS CONE SIZE C	△1					
2377259-3	ELBC-24-SCA-K1-630-B	-	2	-	△2	42	41	18	TYPE SCA B	18.6-24.8 mm
		2377261-3	1	STRESS CONE SIZE B	△1					
2377259-2	ELBC-24-SCA-K1-630-A	-	2	-	△2	42	41	15	TYPE SCA A	15.6-19.5 mm
		2377261-2	1	STRESS CONE SIZE A	△1					
2377259-1	ELBC-24-SCA-K1-630-SA	-	2	-	△2	42	41	13	TYPE SCA SA	13.2-17.5 mm
		2377261-1	1	STRESS CONE SIZE SA	△1					

- △1 MATERIAL: EPDM (CONDUCTIVE)
- △2 MATERIAL: EPDM (INSULATING)
- △3 PRODUCT TYPE IS EXCHANGEABLE (SEE TABLE)
- △4 APPLICATION RANGE IS EXCHANGEABLE (SEE TABLE)

THIS DRAWING IS A CONTROLLED DOCUMENT.

DIMENSIONS: mm	TOLERANCES UNLESS OTHERWISE SPECIFIED:	DWN: L. QIN 24DEC2021	CHK: E. ZHANG 24DEC2021	APVD: W. J. YANG 24DEC2021	NAME: 24kV 630A STRESS CONTROL ADAPTER
0 PLC	±				
1 PLC	±				
2 PLC	±				
3 PLC	±				
4 PLC	±				
ANGLES	±				
FINISH	±				

MATERIAL: SEE TABLE

CUSTOMER DRAWING

SCALE: 2:1 SHEET 1 OF 1 REV: A1