

NUMBER  
C-316535



SEE DWG. NO. C-316531

単位: 画 DIMENSIONS IN MM. DO NOT SCALE PRINT

Copyright © 19 年 Copyright © 19 年  
 AMP (Japan) LTD. ALL RIGHTS RESERVED.  
 日本エー・エム・ピー株式会社

一般公差 (GENERAL TOLERANCE) DIM: ±0.2 HOLE DIA: ±0.25 HOLE LOC: ±0.3 角度: ±3°	適合電線断面積 (WIRE RANGE) mm <sup>2</sup> (AWG)	被覆外径 (INSULATION DIA.) mm φ
	材料 (MATERIAL)	仕上げ (FINISH)

PRINT DIST	A1	REVISED PER ECR-15-018479	NK	NL	05APR16	尺取 (SCALE)	LOC	番号 (No.)	REV.	SHEET
	LTR	変更 (REVISION RECORD)	DR	CHK	DATE	#	A J	C-316535	A1	1 OF 1
	DR.	A.OISHI 8/FEB/99	DE.	Y.NOGUCHI 8/FEB/99	名称 (NAME)		通信ケース 6種 2.5mm シグナル ダブルロック ヘッダーアッシー (Vタイプ) 2.5MM SIGNAL DBL LOCK STD TYPE HDR IN TUBE 6P			
CHK.	Y.NOGUCHI 8/FEB/99	APP.	Y.KASHIWA 8/FEB/99							

AMP-D10-1C  
REV. 3/99

(CUSTOMER DRAWING) 参 考 図 面