





LOC	DIST	REVISIONS					
AI	00	P	LTR	DESCRIPTION	DATE	DWN	APVD
		D		ECR-14-012060	11AUG14	LS	GS



- 1. HEXAGON SOCKET SCREW KEY 2.5 IS FIXED AT HAND TOOL
- 2. INSTRUCTION SHEET IS IN SCOPE OF DELIVERY
TE P/N 5-744001-2
- 3. PACKED IN ONE BOX
- OPTION
- 4. REPAIR KIT, TE P/N 539635-2
CONSISTING OF:
10 DIE RETAINING SCREW, M4x11
11 DIE RETAINING SCREW, M4x10
12 ADJUSTMENT WHEEL
13 RETAINING PLATE 4
14 SCREWED STOP PIN, M3x5
15 TENSION SPRING



SPARE PARTS				
POS	QTY	REV	TE- P/N	DESCRIPTION
2	1	A	519151-9	Linsenkopfschraube, M4x10
3	1	A	8-539634-5	Linsenkopfschraube, M4x11

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN D. Reissig	28JAN99	TE Connectivity	
		CHK U. Reuter	03FEB99		
		APVD U. Reuter	03FEB99	NAME ERGOCRIMP HAND TOOL	
		PRODUCT SPEC		ERGOCRIMP Handzange	
		APPLICATION SPEC		RESTRICTED TO	
DIMENSIONS: mm		TOLERANCES UNLESS OTHERWISE SPECIFIED:		SIZE A3	CAGE CODE 00779
		0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±		DRAWING NO 539635-1	
MATERIAL		FINISH		SCALE 1:1.5	
		Gewicht / Weight in Kg 0.626		SHEET 1 OF 1	
CUSTOMER DRAWING				REV D	