

AMP 1281 (7/63)

APPLICATOR PARTS LIST

AMPLIVAR LENGTHWISE SPLICE PIGTAIL

SPECIAL FLAT ON CRIMPER E ANVIL AMP INCORPORATED HARRISBURG, PENNA. SHIFTER 7-SERR

NO.	DESCRIPTION	REQ.	PART NO.	NO.	DESCRIPTION	REQ.	PART NO.
1	WIRE CRIMPER .125 FLAT	1	455713-2	42	SCREW, SOC. HD. CAP	2	811651-5
2	INS. CRIMPER			43	WASHER, LOCK	2	21057-4
3	ANVIL .125 FLAT	1	455714-2	44	STRIP HOLD DOWN	1	810640-2
4	ANVIL SPACER			45			
5	SHEAR BLADE	1	693012-1	46			
6	REAR SHEAR PLATE	1	465891-1	47			
7	SHEAR BLADE SPACER			48			
8	FRONT SHEAR PLATE			49			
9	REAR ANVIL SPACER PLT.			50	DRAG BUSHING - FRONT	1	452836-1
10	FRONT ANVIL SPACER PLT.			51	DRAG SCREW - FRONT	1	452837-1
11	TOOL SPACER			52	DRAG SPRING - FRONT	1	370572
12	CRIMP SPACER			53			
13	FRONT STRIP GUIDE 1-691311-4	1	<del>691311-6</del>	54	<del>FEED WIRE BRASS</del>	1	<del>22308-1</del>
14	REAR STRIP GUIDE 1-691311-5	1	<del>691311-7</del>	55	ELBOW	1	22317-3
15	RAM	1	471167	56	TUBE	1	689446-2
16	TOOL HOLDER	1	689633-2	57	SCREW, SOC. HD. CAP	1	21001-4
17	ADJ. CRIMP MOUNT & BLADE MT.	1	465755-2	58			
18	SCREW SOC. HD. CAP	1	3-21000-6	59	WASHER, LOCK	1	21024-6
19	APPLICATOR MOUNT ASSY.	1	471707-4	60			
20	BASE PLATE			61	LUBRICATOR ASSY.	1	465184-2
21	BASE BLOCK			62	<del>SYNTHETIC OIL</del>	1	<del>22014-1</del>
22	STRIP GUIDE PLATE			63	AIR BLAST ASSY.	1	455350-2
23	ANVIL HOLDER			64	<del>MECH. TIED</del>	1	<del>692140-2</del>
24	AUX. ANVIL HOLDER			65	TENSION ADJ. PLATE	1	374999
25	STRIPPER - GUARD	1	389072-3	MISCELLANEOUS			
26	STRIPPER MOUNT			66	TOOL SPACER (FOR SET UP ONLY)	1	693619-1
27	RETAINER PLATE			67	NOTE: PLACE ITEM 66 BETWEEN CRIMP		
28	STRIPPER MOUNT BRACKET			68	HOLDER ITEM 17 & ALIGN. GA.		
29	STRIPPER BUSHING			69			
30	STOCK DRAG	1	376666	70			
31	STOCK DRAG HANDLE			71			
32	STOCK DRAG STUD REAR	1	354045-1	72			
33	STOCK DRAG SPRING REAR	1	1-23847-1				
34	STOCK DRAG ADJ. SCREW	2	372997				
35	FEED FINGER HOLDER						
36	FEED FINGER	1	452817-1				
37	FEED FINGER TIP						
38	FEED FINGER SPACER						
39	BASE CASTING	1	570238				
40	R GUARD 460182-1	1	<del>455891-1</del>				
41	F. GUARD BOTTOM (RIGHT)	1	<del>810640-2</del>				
	R 0156-0385-02		3-02 MY/TE				
	L 0150-0500-03		5-03 MY/TE				

CRIMPING DATA				TERMINALS
TO APPLY TERMINAL SPEC 114-2002				62001-62201
WIRE SIZE	CRIMP HEIGHT			
(2) 17 MAG	.080			
CRIMP	SIZE	TYPE	FEED	
WIRE	.140	F		
INSUL.	BLUNT		.315	
SLEEVED				
INSULATION RANGE		WIRE RANGE CMA		
---		3000-7000		
EXPLODED VIEW A-6000 6000-5				
REMARKS: SPECIAL :800 FORWARD				
TOP TOOL MOUNTING FROM TOOL HOLDER (16) OUTWARD ITEMS 17, 5 & 1				
■ DENOTES WEARING PARTS RECOMMEND PURCHASE REPLACEMENT				
THIS APPLICATOR IS TO BE USED ON AMP-O-ELECTRIC 471273-3				
AMP-O-MATIC MECH. FEED ALIGN. GA. 679597-1				DIST. 4
SERIAL NO.		DATE SHIPPED		DESIGNED RUSS 10-471 PROPERTY
CUSTOMER NAME AND ADDRESS				CHK'D. IKM (11-17-71)
				APP'D. (11-02)
APPLICATOR NUMBER	REV. LI	566067-1		SHEET 1 OF 1
		F	DELETE 54 CHG 55, 56 PRESS 9-8-75	R12.75
		G	13 WAS -6 14 WAS -7 11-10-75	R13.82
		H	#44 810640-2 WAS -1 12-10-76	R1892
		J.	ECN. A-395892 9-92	

FOR HARDWARE SEE 7-687500-7

RELEASED FOR PUBLICATION BY AMP INCORPORATED ALL RIGHTS RESERVED

COPYRIGHT 1989