



DETAIL L TYP BOTH ENDS
DETAIL M FOR -6 ONLY

- CONNECTOR MATES WITH ANY 15 POSN PLUG IN AMPLIMITE SERIES & COMPLIES WITH AMP SPEC 108-40005 WHERE APPLICABLE.
- MOLDED PARTS: FLAME RETARDANT 94V-0 RATED THERMOPLASTIC, BLACK.
SHELL: CARBON STEEL.
CONTACTS: PHOSPHOR BRONZE.
EYELETS: BRASS.
SCREWLOCKS: ZINC.
INSERTS: ZINC.
- SHELL: TIN PLATED.
CONTACTS: .000030 GOLD FOR A DISTANCE OF .100 MIN FROM MATING END, TIN PLATED .000100-.000200 ON OPPOSITE END, ALL OVER .000050 NICKEL.
EYELETS: TIN PLATED.
SCREWLOCKS: CLEAR CHROMATE.
INSERTS: CLEAR CHROMATE.

FEMALE SCREWLOCKS	5745782-6
THREADED INSERTS	5745782-4
NONE	5745782-2
MOUNTING HARDWARE	PART NUMBER

**COPYRIGHT 2005
TE CONNECTIVITY CORP
ALL RIGHTS RESERVED**

THIS DRAWING IS A CONTROLLED DOCUMENT.		DIN A FERNANDEZ-DOCKS 04-06-05		TE Connectivity	
DIMENSIONS: INCHES		CHK S BOLASH 04-06-05		RCPT ASSY, SIZE 2, 15 POSN, RTANG, AMPLIMITE HD-20, WITH METAL SHELL, WITH OR WITHOUT SCREWLOCKS OR INSERTS	
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD M WALMSLEY 04-06-05		NAME	
0 PLC ± -		PRODUCT SPEC		108-40025	
1 PLC ± -		APPLICATION SPEC		114-40010	
2 PLC ± -		SIZE		A1	
3 PLC ± .005		CAGE CODE		00779	
4 PLC ± -		DRAWING NO		5745782	
ANGLES ± °		WEIGHT		-	
MATERIAL		FINISH		CUSTOMER DRAWING	
		SCALE		4:1	
		SHEET		1 OF 1	
		REV		R	