


DRAWING NO: FAD0655-0710-6-C
THIS DRAWING IS A CONTROLLED DOCUMENT



CATALOGUE NUMBER: FAD0655-0710-6 SUITS CONDUCTOR

DEADEND

STRANDING	COND. TYPE	DIAMETER	FITTING LAY
7/2.25	AAC/AAAC	6.75	RIGHT HAND
7/0.093	AAC/AAAC	7.09	RIGHT HAND



TECHNICAL SPECIFICATIONS:

CATALOGUE NUMBER: FAD0655-0710-6
DESCRIPTION: FULL-TENSION ALUMINIUM DEADEND
MATERIAL: ALUMINIUM ALLOY
NUMBER OF RODS: 4
ROD DIAMETER: 2.64mm
OVERAL LENGTH: 550mm
END FINISH: CHAMFERED
FITTING LAY DIRECTION: RIGHT HAND
COLOUR CODED: BROWN

PRODUCT LABEL

FAD0655-0710-6
 7/2.25 AAC/AAAC
 7/0.093 AAC/AAAC

WEIGHT: 0.07kg
BATCH NO:
MONTH/YEAR:

BOX LABEL

P/N: FAD0655-0710-6
ID:
DESCRIPTION:
FULL-TENSION ALUMINIUM DEADEND
 7/2.25 AAC/AAAC
 7/0.093 AAC/AAAC
RANGE: 6.55 - 7.10
COLOUR-CODE: BROWN
QTY: 50 **WEIGHT:** **BATCH:**

LOC	DIST	POS	REV	REVISION RECORD	DATE	DWN	APVD	MATERIAL NO	MATL SPEC/STD/DRG NO	PROCESS SPEC HEAT TREAT/PLATING NO	SIZE	PROJECTION	SCALE	DRAWING NO	SHEET	OF	REV
			I	NEW RELEASE	10-05-2013	RN	AT	MATERIAL DESC ALUMINIUM ALLOY			A3	3RD ANGLE	NTS	FAD0655-0710-6-C	1	1	1

THIS INFORMATION IS CONFIDENTIAL AND PROPRIETARY TO TE CONNECTIVITY CORPORATION AND ITS WORLDWIDE SUBSIDIARIES AND AFFILIATES. IT MAY NOT BE DISCLOSED TO ANYONE, OTHER THAN TE CONNECTIVITY PERSONNEL, WITHOUT WRITTEN AUTHORIZATION FROM TE CONNECTIVITY CORPORATION, AUSTRALIA.