



THIS DRAWING IS UNPUBLISHED
 RELEASED FOR PUBLICATION 2017
 © COPYRIGHT 2017 BY - TE CONNECTIVITY ALL RIGHTS RESERVED.

REVISIONS					
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B	REVISED PER PCN E-17-007978	25APR2017	CM	DM

SEAL TYPE	CONTACT SIZE	MIN. INSUL. OD [mm]	MAX. INSUL. OD [mm]	WIRE RANGE [mm ²] REF ONLY
3	NORMAL	.100 [2.540]	.134 [3.404]	14-18 AWG [2.0-.75]
E	16	.053 [1.346]	.120 [3.048]	14-20 AWG [2.0-.50]



4. MATERIAL:
 HOUSING: PPS GF40 (BLACK)
 GROMMET: VMQ (RED-ORANGE)
 THREADED INSERT: STAINLESS STEEL
3. WHEN X = E: LETTER "E" IDENTIFIES "E" WIRE SEAL.
 WHEN X = BLANK: IDENTIFIES "NORMAL" WIRE SEAL (NOT SHOWN).
2. THIS PART MATES WITH DRC16-70SBX-XXXX.
 (XXXX= ALL MODIFICATIONS) CONSULT FACTORY FOR MODS.
1. RECEPTACLE IS SUPPLIED WITH DUST CAP (NOT SHOWN).

NOTES: UNLESS OTHERWISE SPECIFIED

TE INTERNAL PN	DEUTSCH PN
DRC14-70PB	DRC14-70PB
DRC14-70PBE	DRC14-70PBE

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN J. APOSTOL 13NOV2012		
DIMENSIONS: INCHES [mm]		CHK D. HASIBUAN 15FEB2013		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD D. MEYER 18FEB2013		
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ±.025 [0.64] 4 PLC ± ANGLES ±0° 30' 0"		PRODUCT SPEC -		
MATERIAL 4		FINISH -	NAME RECEPTACLE, INLINE 70 PIN, SIZE 16 DRC SERIES KEY ARRANGEMENT -B-	
		WEIGHT -	SIZE A3	CAGE CODE 4AFU8
			DRAWING NO. DRC14-70PBX	
			RESTRICTED TO -	
			SCALE 1:1	SHEET 1 OF 1
			REV B	