




THIS DRAWING IS UNPUBLISHED  
 RELEASED FOR PUBLICATION 2014  
 © COPYRIGHT 2001 BY TE CONNECTIVITY ALL RIGHTS RESERVED.

LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	A	REVISED PER E.O. PI7348	24SEP2001	PB	RDR
	B	REVISED PER E.O. PI9404	20NOV2006	PB	RDR
	B1	REVISED PER ECO-14-010107	03JUL2014	JA	DM
	B2	REVISED PER ECR-14-016969	10NOV2014	JA	DM




6. MOUNTING SCREW TORQUE VALUES ARE AS FOLLOWS:  
 #6-19 SCREWS: 13±2.0 IN-LB [1.47±0.23 N-M].  
 #4-20 SCREWS: 8±2.0 IN-LB [.90±0.23 N-M].  
 VALUES VALID FOR PLASTITE 48 SCREWS ONLY.
5. RECOMMENDED MOUNTING SCREWS (NOT INCLUDED):  
 CAMCAR PLASTITE 48, SINGLE HELIX.
4. THIS RECEPTACLE MATES WITH DT06-4S-XXXX PLUG  
 (XXXX = ALL MODIFICATIONS).
3. CONTACT PLATING (G003) - MATING SIDE: GOLD; PCB SIDE: TIN.

TE INTERNAL PN	DEUTSCH PN
DT13-4P-G003	DT13-4P-G003

- 2 MATERIALS:  
 SHELL: PA GF30 (GRAY)  
 SEAL: SILICONE (ORANGE-RED)  
 PIN CONTACTS: COPPER ALLOY
- 1 DIMENSION TOLERANCE: ±.025 [.64]  
 PANEL CUTOUT: ±.010 [.25].  
 PIN LOCATIONS: ±.005 [.13]  
 MOUNTING HOLE LOCATIONS: ±.010 [.13]

NOTES:

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PAUL BURKE 21SEP2001	 TE Connectivity	
DIMENSIONS: INCHES [mm]		CHK PAUL BURKE 21SEP2001		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		APVD STEVE BEARD 21SEP2001	NAME RECEPTACLE HEADER 4 PIN 90 DEG DT SERIES	
0 PLC ± 1 PLC ± 2 PLC ± 3 PLC ± 4 PLC ± ANGLES ±0°30'0"		PRODUCT SPEC	RESTRICTED TO	
MATERIAL		APPLICATION SPEC	SIZE A3	CAGE CODE 4AFU8
FINISH		WEIGHT 22g±10%	DRAWING NO DT13-4P-G003	
2		Customer Drawing	SCALE 3:2	SHEET 1 OF 2
			REV B2	

4

3

2

1

THIS DRAWING IS UNPUBLISHED. RELEASED FOR PUBLICATION 2014

© COPYRIGHT 2001 BY TE CONNECTIVITY ALL RIGHTS RESERVED.




LOC	DIST	REVISIONS			
P	LTR	DESCRIPTION	DATE	DWN	APVD
	B2	SEE SHEET 1	10NOV2014	JA	DM

Dimensions:  
 .152 [3.86]  
 .816 [20.73]  
 .860 [21.84]  
 1.120 [28.45]  
 2X  $\phi$ .155 [3.94]  
 4X R.220 [5.59]  
 2X R.020 [.51]  
 2X R.060 [1.52]

Dimensions:  
 .152 [3.86]  
 .816 [20.73]  
 .860 [21.84]  
 1.120 [28.45]  
 2X  $\phi$ .155 [3.94]  
 4X R.250 [6.35]

DATE CODE

### RECOMMENDED PANEL CUTOUTS

THIS DRAWING IS A CONTROLLED DOCUMENT.		DWN PAUL BURKE 21SEP2001	 TE Connectivity		
DIMENSIONS: INCHES [mm]		CHK PAUL BURKE 21SEP2001			
		APVD STEVE BEARD 21SEP2001	NAME RECEPTACLE HEADER 4 PIN 90 DEG DT SERIES		
TOLERANCES UNLESS OTHERWISE SPECIFIED:		PRODUCT SPEC	RESTRICTED TO		
0 PLC $\pm$ 1 PLC $\pm$ 2 PLC $\pm$ 3 PLC $\pm$ 4 PLC $\pm$ ANGLES $\pm 0^{\circ}30'0''$		APPLICATION SPEC	SIZE A3	CAGE CODE 4AFU8	DRAWING NO DT13-4P-G003
MATERIAL 		FINISH	WEIGHT 22g $\pm$ 10%	SCALE 3:2	SHEET 2 OF 2
		Customer Drawing	REV B2		

1470-19 (3/11)