

REV		REVISIONS			
NC	DTMH04-3P*	SYM	DESCRIPTION	DATE	APPROVED
NC			NEW RELEASE PER E.O. P19881	9-15-08	SA

- 8 SEE SHEET 2 FOR OTHER KEY ARRANGEMENTS.
- 7. RECEPTACLE IS RATED AT 150°C.
- 6. MATERIAL - HOUSING: PLASTIC; GROMMET: RUBBER.
- 5. THIS RECEPTACLE MATES WITH DTMH06-3S-**** AND DTM06-3S-**** PLUG. (**** = ALL MODIFICATIONS)
- 4 FOR CONTACT AND WIRE PERFORMANCE AND APPLICATION CHARACTERISTICS SEE ENVELOPE DRAWING 0425-015-0000.
- 3 TERMINAL POSITION ASSURANCE (TPA) LOCK PRE-MOUNTED: WMH-4P* (* = A,B,C,D KEYS).
- 2. DIMENSION TOLERANCE: ±.025 [.64].
- 1. DIMENSIONS ARE IN INCHES [mm].

NOTES: UNLESS OTHERWISE SPECIFIED

CONTACT SIZE	MIN. INSUL. O.D.	MAX. INSUL. O.D.	WIRE RANGE [mm ²] REF ONLY
20	.053 [1.35]	.120 [3.05]	16-20 AWG [1.0-0.5]






SIGNATURE & DATE	
DR	J. APOSTOL 28DEC2007
CHK	B. [Signature] 9/10/08
PE	D. Whitace 8/1/08
APPD	D. [Signature] 9/2/08
SCALE	NONE

RECEPTACLE
3 PIN CONT. #20
COLOR: BLACK
DTMH SERIES


ENVELOPE

EP 180	MATL. CODE
3850 INDUSTRIAL AVE. HEMET, CA 92545	
DEUTSCH INDUSTRIAL	
B	DTMH04-3P*
DWG SIZE	CODE 11139 SHEET 1 OF 2


REV NC	DTMH04-3P*	REVISIONS			
		SYM	DESCRIPTION	DATE	APPROVED
			SEE SHEET 1	9.15.08	SB




DTMH04-3PA
-A- KEY
TPA COLOR: GREY



DTMH04-3PB
-B- KEY
TPA COLOR: BLACK



DTMH04-3PC
-C- KEY
TPA COLOR: GREEN



DTMH04-3PD
-D- KEY
TPA COLOR: BROWN

NOTES:

SIGNATURE & DATE		RECEPTACLE 3 PIN CONT. #20 COLOR: BLACK DTMH SERIES	EP 180	MATL. CODE
DR	J. APOSTOL 28DEC2007		3850 INDUSTRIAL AVE. HEMET, CA 92545	
CHK	<i>[Signature]</i> 9/10/08		DEUTSCH INDUSTRIAL	
PE	<i>[Signature]</i> 8/1/08		B DTMH04-3P*	
APPD	<i>[Signature]</i> 7/2/08	ENVELOPE	DWG SIZE	CODE 11139
SCALE	NONE			SHEET 2 OF 2